

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266678

Luminaire Tested: P3AS05R359735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 240.0 lumens
Efficiency: N/A
Efficacy: 33.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266678

CATALOG NUMBER: P3AS05R359735DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266678

CATALOG NUMBER: P3AS05R359735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		85
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		80
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		76
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		73
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		70
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		66
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		64
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121043
5°	116333
10°	101356
15°	77639
20°	51945
25°	31429
30°	18028
35°	10092
40°	5353
45°	2760
50°	1330
55°	1032
60°	1009
65°	830
70°	898
75°	763
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2760 cd/sqm

TEST NUMBER: P1266678

CATALOG NUMBER: P3AS05R359735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	20.0
10°-20°	93.2	38.8
20°-30°	61.0	25.4
30°-40°	24.7	10.3
40°-50°	7.4	3.1
50°-60°	2.5	1.1
60°-70°	1.7	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.3	84.3
0°-40°	227.0	94.6
0°-60°	237.0	98.7
0°-90°	240.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	240.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	552	
5°	528	48
15°	342	93
25°	130	61
35°	38	25
45°	9	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1266678

CATALOG NUMBER: P3AS05R359735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	552.0
1°	551.1
2°	548.6
3°	543.6
4°	537.6
5°	528.5
6°	517.1
7°	504.3
8°	489.9
9°	473.5
10°	455.2
11°	434.9
12°	413.7
13°	389.9
14°	367.3
15°	342.0
17.5°	280.6
20°	222.6
22.5°	171.2
25°	129.9
27.5°	96.8
30°	71.2
32.5°	52.3
35°	37.7
37.5°	26.7
40°	18.7
42.5°	13.0
45°	8.9
47.5°	5.9
50°	3.9
52.5°	3.0
55°	2.7
57.5°	2.5
60°	2.3
62.5°	2.1
65°	1.6
67.5°	1.4
70°	1.4
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.7
82.5°	0.5
85°	0.2
87.5°	0.2



TEST NUMBER: P1266678

CATALOG NUMBER: P3AS05R359735DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)