

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266689

Luminaire Tested: P3AS05R359735DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266689
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359735DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 376.9 lumens
Efficiency: N/A
Efficacy: 52.3 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266689

CATALOG NUMBER: P3AS05R359735DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1266689

CATALOG NUMBER: P3AS05R359735DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86112
5°	84283
10°	78934
15°	70852
20°	61629
25°	52527
30°	44007
35°	35041
40°	25333
45°	16033
50°	8733
55°	6040
60°	5701
65°	5292
70°	5065
75°	4321
80°	4167
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16033 cd/sqm

TEST NUMBER: P1266689

CATALOG NUMBER: P3AS05R359735DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.6	9.5
10°-20°	86.9	23.0
20°-30°	99.5	26.4
30°-40°	81.2	21.5
40°-50°	40.9	10.9
50°-60°	15.2	4.0
60°-70°	10.2	2.7
70°-80°	5.6	1.5
80°-90°	1.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.0	58.9
0°-40°	303.3	80.5
0°-60°	359.4	95.4
0°-90°	376.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	376.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	393	
5°	383	36
15°	312	87
25°	217	100
35°	131	81
45°	52	41
55°	16	15
65°	10	10
75°	5	6
85°	1	2
90°	0	

TEST NUMBER: P1266689

CATALOG NUMBER: P3AS05R359735DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	392.7
1°	392.3
2°	391.3
3°	389.5
4°	386.7
5°	382.9
6°	378.3
7°	373.6
8°	367.6
9°	361.5
10°	354.5
11°	347.1
12°	339.2
13°	330.3
14°	321.0
15°	312.1
17.5°	288.4
20°	264.1
22.5°	239.5
25°	217.1
27.5°	195.2
30°	173.8
32.5°	152.3
35°	130.9
37.5°	109.5
40°	88.5
42.5°	68.9
45°	51.7
47.5°	37.3
50°	25.6
52.5°	18.6
55°	15.8
57.5°	14.4
60°	13.0
62.5°	11.6
65°	10.2
67.5°	8.9
70°	7.9
72.5°	6.5
75°	5.1
77.5°	4.2
80°	3.3
82.5°	2.3
85°	1.4
87.5°	0.9



TEST NUMBER: P1266689

CATALOG NUMBER: P3AS05R359735DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)