

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267443

Luminaire Tested: P3AS13R309735DE010 E3DL1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1267443  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R309735DE010 E3DL1WH  
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 584.0 lumens  
Efficiency: N/A  
Efficacy: 40.0 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267443  
CATALOG NUMBER: P3AS13R309735DE010 E3DL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1267443

CATALOG NUMBER: P3AS13R309735DE010 E3DL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	199567
5°	193352
10°	174212
15°	144110
20°	111566
25°	83690
30°	60769
35°	40475
40°	24875
45°	14606
50°	8972
55°	7264
60°	6359
65°	5189
70°	4616
75°	4575
80°	3410
85°	4529

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14606 cd/sqm



TEST NUMBER: P1267443  
 CATALOG NUMBER: P3AS13R309735DE010 E3DL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.8	13.8
10°-20°	174.8	29.9
20°-30°	159.1	27.2
30°-40°	96.2	16.5
40°-50°	38.6	6.6
50°-60°	17.1	2.9
60°-70°	10.3	1.8
70°-80°	5.6	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	414.7	71.0
0°-40°	510.9	87.5
0°-60°	566.5	97.0
0°-90°	584.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	584.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	910	
5°	878	81
15°	635	175
25°	346	159
35°	151	96
45°	47	39
55°	19	17
65°	10	10
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1267443  
CATALOG NUMBER: P3AS13R309735DE010 E3DL1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	910.1
1°	909.2
2°	905.6
3°	899.2
4°	890.2
5°	878.4
6°	863.9
7°	848.5
8°	828.6
9°	805.9
10°	782.4
11°	755.2
12°	726.3
13°	697.3
14°	665.6
15°	634.8
17.5°	554.2
20°	478.1
22.5°	407.5
25°	345.9
27.5°	289.8
30°	240.0
32.5°	193.8
35°	151.2
37.5°	115.9
40°	86.9
42.5°	63.4
45°	47.1
47.5°	35.3
50°	26.3
52.5°	20.8
55°	19.0
57.5°	16.3
60°	14.5
62.5°	11.8
65°	10.0
67.5°	9.1
70°	7.2
72.5°	6.3
75°	5.4
77.5°	4.5
80°	2.7
82.5°	1.8
85°	1.8
87.5°	0.9



TEST NUMBER: P1267443  
CATALOG NUMBER: P3AS13R309735DE010 E3DL1WH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)