

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266776

Luminaire Tested: P3AS05R509735DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266776
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509735DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 169.0 lumens
Efficiency: N/A
Efficacy: 23.5 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266776

CATALOG NUMBER: P3AS05R509735DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266776

CATALOG NUMBER: P3AS05R509735DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	106	103		104	102	100		100	99	97		97	95	94
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	95	89	85		99	93	88	85		91	87	83		88	85	82		86	83	81
4	96	88	82	78		94	87	82	78		85	80	77		83	79	76		81	78	75
5	91	83	76	72		90	82	76	72		80	75	71		78	74	70		77	73	70
6	87	77	71	67		85	77	71	67		75	70	66		74	69	66		72	68	65
7	82	73	67	62		81	72	66	62		71	66	62		70	65	61		68	64	61
8	78	69	63	58		77	68	62	58		67	62	58		66	61	58		65	61	57
9	75	65	59	55		74	64	59	55		63	58	55		63	58	54		62	57	54
10	71	61	56	52		70	61	55	52		60	55	51		59	55	51		59	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49163
5°	47832
10°	44110
15°	38797
20°	32459
25°	25743
30°	18889
35°	12983
40°	8244
45°	4621
50°	2490
55°	2103
60°	1798
65°	1660
70°	1475
75°	1356
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4621 cd/sqm

TEST NUMBER: P1266776

CATALOG NUMBER: P3AS05R509735DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.1	11.9
10°-20°	47.3	28.0
20°-30°	48.4	28.6
30°-40°	30.7	18.2
40°-50°	12.2	7.2
50°-60°	5.0	2.9
60°-70°	3.2	1.9
70°-80°	1.6	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.9	68.6
0°-40°	146.6	86.7
0°-60°	163.7	96.9
0°-90°	169.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	169.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	224	
5°	217	20
15°	171	47
25°	106	48
35°	48	31
45°	15	12
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1266776

CATALOG NUMBER: P3AS05R509735DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	224.2
2.5°	222.6
5°	217.3
7.5°	209.1
10°	198.1
12.5°	185.0
15°	170.9
17.5°	155.3
20°	139.1
22.5°	122.8
25°	106.4
27.5°	89.9
30°	74.6
32.5°	60.8
35°	48.5
37.5°	38.0
40°	28.8
42.5°	21.3
45°	14.9
47.5°	10.1
50°	7.3
52.5°	6.2
55°	5.5
57.5°	4.8
60°	4.1
62.5°	3.7
65°	3.2
67.5°	2.7
70°	2.3
72.5°	1.8
75°	1.6
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)