

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267555

Luminaire Tested: P3AS13R509735DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509735DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1019.0 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267555
CATALOG NUMBER: P3AS13R509735DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1267555
 CATALOG NUMBER: P3AS13R509735DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76	76	76	76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67	67	67	67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64	64	64	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57	57	57	57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54	54	54	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	324426
5°	317895
10°	297768
15°	266562
20°	224323
25°	171203
30°	111258
35°	65959
40°	38129
45°	19103
50°	7096
55°	5543
60°	5175
65°	4722
70°	4616
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19103 cd/sqm



TEST NUMBER: P1267555
 CATALOG NUMBER: P3AS13R509735DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.4	13.2
10°-20°	324.7	31.9
20°-30°	318.6	31.3
30°-40°	160.5	15.7
40°-50°	50.7	5.0
50°-60°	13.1	1.3
60°-70°	9.3	0.9
70°-80°	5.7	0.6
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	777.7	76.3
0°-40°	938.1	92.1
0°-60°	1002.0	98.3
0°-90°	1019.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1019.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1480	
5°	1444	134
15°	1174	325
25°	708	319
35°	246	160
45°	62	51
55°	14	13
65°	9	9
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1267555
CATALOG NUMBER: P3AS13R509735DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1479.5
2.5°	1470.5
5°	1444.2
7.5°	1397.1
10°	1337.3
12.5°	1260.3
15°	1174.2
17.5°	1074.5
20°	961.3
22.5°	839.0
25°	707.6
27.5°	568.1
30°	439.4
32.5°	330.7
35°	246.4
37.5°	182.1
40°	133.2
42.5°	94.2
45°	61.6
47.5°	35.3
50°	20.8
52.5°	15.4
55°	14.5
57.5°	12.7
60°	11.8
62.5°	10.9
65°	9.1
67.5°	8.2
70°	7.2
72.5°	6.3
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)