

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266799

Luminaire Tested: P3AS05R559735DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1266799  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R559735DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 194.0 lumens  
Efficiency: N/A  
Efficacy: 26.9 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266799  
CATALOG NUMBER: P3AS05R559735DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1266799  
 CATALOG NUMBER: P3AS05R559735DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	96	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	36466
5°	36011
10°	34602
15°	32350
20°	29519
25°	26324
30°	23042
35°	19140
40°	15085
45°	10234
50°	6243
55°	3250
60°	3026
65°	2854
70°	2629
75°	2288
80°	2273
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10234 cd/sqm



TEST NUMBER: P1266799  
 CATALOG NUMBER: P3AS05R559735DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	15.3	7.9
10°-20°	39.8	20.5
20°-30°	49.9	25.7
30°-40°	44.5	23.0
40°-50°	26.1	13.4
50°-60°	9.0	4.6
60°-70°	5.4	2.8
70°-80°	3.0	1.5
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	105.1	54.2
0°-40°	149.6	77.1
0°-60°	184.7	95.2
0°-90°	194.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	194.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	166	
5°	164	15
15°	142	40
25°	109	50
35°	72	45
45°	33	26
55°	8	9
65°	6	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1266799  
CATALOG NUMBER: P3AS05R559735DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	166.3
2.5°	165.4
5°	163.6
7.5°	159.9
10°	155.4
12.5°	149.6
15°	142.5
17.5°	135.0
20°	126.5
22.5°	117.8
25°	108.8
27.5°	99.9
30°	91.0
32.5°	81.3
35°	71.5
37.5°	61.9
40°	52.7
42.5°	42.8
45°	33.0
47.5°	25.2
50°	18.3
52.5°	11.9
55°	8.5
57.5°	7.6
60°	6.9
62.5°	6.2
65°	5.5
67.5°	4.8
70°	4.1
72.5°	3.4
75°	2.7
77.5°	2.3
80°	1.8
82.5°	1.1
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)