

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267597

Luminaire Tested: P3AS13R559735DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559735DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 659.0 lumens
Efficiency: N/A
Efficacy: 45.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267597

CATALOG NUMBER: P3AS13R559735DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1267597

CATALOG NUMBER: P3AS13R559735DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	70	50	30	10	70	50	30	10	70	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79			
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55			
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52			
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	179262
5°	174774
10°	162478
15°	144700
20°	122954
25°	99223
30°	75657
35°	53806
40°	35495
45°	21056
50°	12349
55°	7608
60°	6754
65°	6123
70°	5193
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21056 cd/sqm

TEST NUMBER: P1267597

CATALOG NUMBER: P3AS13R559735DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.7	11.2
10°-20°	176.7	26.8
20°-30°	187.2	28.4
30°-40°	126.5	19.2
40°-50°	55.4	8.4
50°-60°	19.8	3.0
60°-70°	11.7	1.8
70°-80°	6.1	0.9
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	437.6	66.4
0°-40°	564.0	85.6
0°-60°	639.3	97.0
0°-90°	659.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	659.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	818	
5°	794	74
15°	637	177
25°	410	187
35°	201	126
45°	68	55
55°	20	20
65°	12	12
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1267597

CATALOG NUMBER: P3AS13R559735DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	817.5
2.5°	811.2
5°	794.0
7.5°	765.9
10°	729.7
12.5°	686.3
15°	637.4
17.5°	583.0
20°	526.9
22.5°	468.1
25°	410.1
27.5°	353.1
30°	298.8
32.5°	247.2
35°	201.0
37.5°	159.3
40°	124.0
42.5°	93.3
45°	67.9
47.5°	49.8
50°	36.2
52.5°	25.3
55°	19.9
57.5°	18.1
60°	15.4
62.5°	13.6
65°	11.8
67.5°	10.0
70°	8.1
72.5°	7.2
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)