

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267605

Luminaire Tested: P3AS13R609735DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609735DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1171.0 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267605

CATALOG NUMBER: P3AS13R609735DE010 E3CD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1267605

CATALOG NUMBER: P3AS13R609735DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	279627
5°	268544
10°	276481
15°	280024
20°	247285
25°	208391
30°	169013
35°	110075
40°	50552
45°	19382
50°	6482
55°	1720
60°	1579
65°	1401
70°	1154
75°	1525
80°	1137
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19382 cd/sqm

TEST NUMBER: P1267605

CATALOG NUMBER: P3AS13R609735DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	10.0
10°-20°	337.8	28.8
20°-30°	394.0	33.6
30°-40°	254.3	21.7
40°-50°	57.0	4.9
50°-60°	5.7	0.5
60°-70°	2.7	0.2
70°-80°	1.5	0.1
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	849.2	72.5
0°-40°	1103.5	94.2
0°-60°	1166.1	99.6
0°-90°	1171.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1171.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1275	
5°	1220	117
15°	1234	338
25°	861	394
35°	411	254
45°	62	57
55°	4	6
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1267605

CATALOG NUMBER: P3AS13R609735DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1275.2
2.5°	1254.4
5°	1220.0
7.5°	1218.1
10°	1241.7
12.5°	1257.1
15°	1233.5
17.5°	1162.9
20°	1059.7
22.5°	951.9
25°	861.3
27.5°	772.6
30°	667.5
32.5°	544.3
35°	411.2
37.5°	280.8
40°	176.6
42.5°	106.0
45°	62.5
47.5°	36.2
50°	19.0
52.5°	6.3
55°	4.5
57.5°	3.6
60°	3.6
62.5°	2.7
65°	2.7
67.5°	2.7
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)