

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267627

Luminaire Tested: P3AS13R609735DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267627
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609735DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 952.0 lumens
Efficiency: N/A
Efficacy: 65.2 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267627

CATALOG NUMBER: P3AS13R609735DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1267627

CATALOG NUMBER: P3AS13R609735DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	224807
5°	222672
10°	216184
15°	202544
20°	179262
25°	149960
30°	117537
35°	85260
40°	56735
45°	35353
50°	19138
55°	5543
60°	5175
65°	4670
70°	4616
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35353 cd/sqm

TEST NUMBER: P1267627

CATALOG NUMBER: P3AS13R609735DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.3	10.0
10°-20°	247.5	26.0
20°-30°	282.1	29.6
30°-40°	200.1	21.0
40°-50°	90.8	9.5
50°-60°	19.3	2.0
60°-70°	9.3	1.0
70°-80°	5.7	0.6
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	624.9	65.6
0°-40°	825.0	86.7
0°-60°	935.1	98.2
0°-90°	952.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	952.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1025	
5°	1012	95
15°	892	248
25°	620	282
35°	318	200
45°	114	91
55°	14	19
65°	9	9
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1267627

CATALOG NUMBER: P3AS13R609735DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1025.2
2.5°	1021.5
5°	1011.6
7.5°	994.4
10°	970.9
12.5°	937.4
15°	892.2
17.5°	835.1
20°	768.2
22.5°	695.8
25°	619.8
27.5°	542.0
30°	464.2
32.5°	390.0
35°	318.5
37.5°	255.2
40°	198.2
42.5°	150.2
45°	114.0
47.5°	85.1
50°	56.1
52.5°	26.2
55°	14.5
57.5°	12.7
60°	11.8
62.5°	10.9
65°	9.0
67.5°	8.1
70°	7.2
72.5°	6.3
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)