

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266886

Luminaire Tested: P3AS05R709735DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266886
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709735DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 164.0 lumens
Efficiency: N/A
Efficacy: 22.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266886

CATALOG NUMBER: P3AS05R709735DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266886

CATALOG NUMBER: P3AS05R709735DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38462
5°	37750
10°	35604
15°	32304
20°	28259
25°	23832
30°	19522
35°	15151
40°	10849
45°	6853
50°	3411
55°	2103
60°	1798
65°	1660
70°	1475
75°	1356
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6853 cd/sqm

TEST NUMBER: P1266886

CATALOG NUMBER: P3AS05R709735DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.0	9.8
10°-20°	39.6	24.2
20°-30°	45.1	27.5
30°-40°	35.3	21.5
40°-50°	17.3	10.6
50°-60°	5.3	3.2
60°-70°	3.1	1.9
70°-80°	1.7	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	100.7	61.4
0°-40°	136.0	82.9
0°-60°	158.6	96.7
0°-90°	164.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	164.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	175	
5°	172	16
15°	142	40
25°	98	45
35°	57	35
45°	22	17
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1266886

CATALOG NUMBER: P3AS05R709735DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	175.4
2.5°	174.5
5°	171.5
7.5°	166.8
10°	159.9
12.5°	151.9
15°	142.3
17.5°	132.1
20°	121.1
22.5°	109.7
25°	98.5
27.5°	87.6
30°	77.1
32.5°	66.6
35°	56.6
37.5°	47.0
40°	37.9
42.5°	29.4
45°	22.1
47.5°	15.5
50°	10.0
52.5°	6.6
55°	5.5
57.5°	4.8
60°	4.1
62.5°	3.6
65°	3.2
67.5°	2.7
70°	2.3
72.5°	1.8
75°	1.6
77.5°	1.4
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)