

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267652

Luminaire Tested: P3AS13R659735DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659735DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 308.0 lumens
Efficiency: N/A
Efficacy: 21.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267652

CATALOG NUMBER: P3AS13R659735DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1267652

CATALOG NUMBER: P3AS13R659735DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78283
5°	76337
10°	71096
15°	63701
20°	55025
25°	45777
30°	36082
35°	26742
40°	18435
45°	11443
50°	6209
55°	3900
60°	3289
65°	3009
70°	2565
75°	2288
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11443 cd/sqm

TEST NUMBER: P1267652

CATALOG NUMBER: P3AS13R659735DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.2	10.5
10°-20°	78.0	25.3
20°-30°	86.2	28.0
30°-40°	62.6	20.3
40°-50°	29.3	9.5
50°-60°	9.9	3.2
60°-70°	5.7	1.9
70°-80°	3.0	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.5	63.8
0°-40°	259.1	84.1
0°-60°	298.3	96.9
0°-90°	308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	357	
5°	347	32
15°	281	78
25°	189	86
35°	100	63
45°	37	29
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1267652

CATALOG NUMBER: P3AS13R659735DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	357.0
2.5°	354.8
5°	346.8
7.5°	334.8
10°	319.3
12.5°	301.1
15°	280.6
17.5°	258.4
20°	235.8
22.5°	212.3
25°	189.2
27.5°	165.6
30°	142.5
32.5°	120.3
35°	99.9
37.5°	81.3
40°	64.4
42.5°	49.3
45°	36.9
47.5°	26.6
50°	18.2
52.5°	12.4
55°	10.2
57.5°	8.9
60°	7.5
62.5°	6.7
65°	5.8
67.5°	4.9
70°	4.0
72.5°	3.6
75°	2.7
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)