

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266951

Luminaire Tested: P3AS09R159735DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1266951  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R159735DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 420.0 lumens  
Efficiency: N/A  
Efficacy: 37.8 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266951  
CATALOG NUMBER: P3AS09R159735DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1266951  
 CATALOG NUMBER: P3AS09R159735DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	98
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	92	91
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	85	84
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	79	78
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	74	73
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	69	68
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	65	64
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	61	60
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	58	57
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	55	54
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	52	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	181104
5°	167400
10°	133643
15°	100954
20°	76867
25°	58576
30°	41956
35°	27385
40°	16803
45°	10141
50°	6755
55°	5199
60°	4473
65°	3891
70°	3526
75°	3474
80°	2526
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10141 cd/sqm



TEST NUMBER: P1266951  
 CATALOG NUMBER: P3AS09R159735DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.4	16.0
10°-20°	124.3	29.6
20°-30°	110.7	26.3
30°-40°	65.5	15.6
40°-50°	26.9	6.4
50°-60°	12.6	3.0
60°-70°	7.7	1.8
70°-80°	4.0	1.0
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	302.3	72.0
0°-40°	367.8	87.6
0°-60°	407.2	97.0
0°-90°	420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	420.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	826	
5°	760	67
15°	445	124
25°	242	111
35°	102	65
45°	33	27
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1266951  
CATALOG NUMBER: P3AS09R159735DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	825.9
1°	823.9
2°	817.8
3°	805.5
4°	785.0
5°	760.5
6°	733.9
7°	702.5
8°	669.8
9°	636.3
10°	600.2
12.5°	517.7
15°	444.7
17.5°	381.9
20°	329.4
22.5°	283.0
25°	242.1
27.5°	202.6
30°	165.7
32.5°	132.3
35°	102.3
37.5°	78.4
40°	58.7
42.5°	43.7
45°	32.7
47.5°	25.2
50°	19.8
52.5°	16.4
55°	13.6
57.5°	11.6
60°	10.2
62.5°	8.9
65°	7.5
67.5°	6.8
70°	5.5
72.5°	4.8
75°	4.1
77.5°	2.7
80°	2.0
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)