

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267735

Luminaire Tested: P3AS17R209735DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209735DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 944.1 lumens
Efficiency: N/A
Efficacy: 44.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267735

CATALOG NUMBER: P3AS17R209735DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1267735

CATALOG NUMBER: P3AS17R209735DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55		
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52		
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48		
10	68	58	51	47	67	57	51	47	56	51	47	56	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	233490
5°	227272
10°	209059
15°	184019
20°	157817
25°	132588
30°	107181
35°	81539
40°	58023
45°	38299
50°	23743
55°	15598
60°	14209
65°	13075
70°	12310
75°	11184
80°	10607
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38299 cd/sqm

TEST NUMBER: P1267735

CATALOG NUMBER: P3AS17R209735DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	10.1
10°-20°	225.7	23.9
20°-30°	250.5	26.5
30°-40°	191.1	20.2
40°-50°	97.9	10.4
50°-60°	40.2	4.3
60°-70°	25.1	2.7
70°-80°	14.1	1.5
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	571.7	60.6
0°-40°	762.8	80.8
0°-60°	900.8	95.4
0°-90°	944.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	944.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1065	
5°	1032	96
15°	811	226
25°	548	250
35°	305	191
45°	124	98
55°	41	40
65°	25	25
75°	13	14
85°	4	4
90°	0	

TEST NUMBER: P1267735

CATALOG NUMBER: P3AS17R209735DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1064.8
1°	1066.0
2°	1061.2
3°	1055.2
4°	1045.7
5°	1032.5
6°	1016.9
7°	1000.1
8°	982.1
9°	960.5
10°	938.9
12.5°	876.6
15°	810.6
17.5°	743.5
20°	676.3
22.5°	609.2
25°	548.0
27.5°	486.9
30°	423.3
32.5°	363.3
35°	304.6
37.5°	253.0
40°	202.7
42.5°	159.5
45°	123.5
47.5°	93.5
50°	69.6
52.5°	51.6
55°	40.8
57.5°	37.2
60°	32.4
62.5°	28.8
65°	25.2
67.5°	21.6
70°	19.2
72.5°	15.6
75°	13.2
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2
90°	0.0

(END OF REPORT)