

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267768

Luminaire Tested: P3AS17R259735DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1267768  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R259735DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1256.0 lumens  
Efficiency: N/A  
Efficacy: 59.2 lumens/watt  
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267768

CATALOG NUMBER: P3AS17R259735DE010 E3DLP1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1267768

CATALOG NUMBER: P3AS17R259735DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 110 | 108 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  | 98  | 97  |
| 2   | 110 | 105 | 102 | 99  |  | 107 | 104 | 101 | 98  |  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  | 93  | 92  |
| 3   | 105 | 100 | 96  | 92  |  | 103 | 98  | 95  | 91  |  | 96  | 93  | 90  |  | 94  | 91  | 89  |  | 91  | 89  | 87  |
| 4   | 101 | 95  | 90  | 87  |  | 99  | 94  | 89  | 86  |  | 92  | 88  | 85  |  | 90  | 87  | 84  |  | 88  | 85  | 83  |
| 5   | 97  | 90  | 85  | 82  |  | 96  | 89  | 85  | 81  |  | 88  | 84  | 81  |  | 86  | 83  | 80  |  | 85  | 82  | 79  |
| 6   | 94  | 86  | 81  | 78  |  | 92  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 83  | 79  | 77  |  | 82  | 78  | 76  |
| 7   | 90  | 83  | 78  | 74  |  | 89  | 82  | 77  | 74  |  | 81  | 77  | 74  |  | 80  | 76  | 73  |  | 79  | 75  | 73  |
| 8   | 87  | 79  | 74  | 71  |  | 86  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  | 73  | 70  |
| 9   | 84  | 76  | 71  | 68  |  | 83  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 68  |  | 73  | 70  | 67  |
| 10  | 81  | 73  | 69  | 65  |  | 80  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 67  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 805681 |
| 5°  | 751682 |
| 10° | 602149 |
| 15° | 408742 |
| 20° | 247332 |
| 25° | 144637 |
| 30° | 82367  |
| 35° | 45294  |
| 40° | 24045  |
| 45° | 12652  |
| 50° | 7369   |
| 55° | 5505   |
| 60° | 4736   |
| 65° | 4981   |
| 70° | 4616   |
| 75° | 4067   |
| 80° | 3031   |
| 85° | 3019   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12652 cd/sqm

TEST NUMBER: P1267768

CATALOG NUMBER: P3AS17R259735DE010 E3DLP1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 303.0  | 24.1      |
| 10°-20°   | 495.0  | 39.4      |
| 20°-30°   | 282.9  | 22.5      |
| 30°-40°   | 111.6  | 8.9       |
| 40°-50°   | 34.2   | 2.7       |
| 50°-60°   | 13.5   | 1.1       |
| 60°-70°   | 9.1    | 0.7       |
| 70°-80°   | 5.1    | 0.4       |
| 80°-90°   | 1.6    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1080.9 | 86.1      |
| 0°-40°    | 1192.5 | 94.9      |
| 0°-60°    | 1240.2 | 98.7      |
| 0°-90°    | 1256.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1256.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3674 |      |
| 5°  | 3415 | 303  |
| 15° | 1800 | 495  |
| 25° | 598  | 283  |
| 35° | 169  | 112  |
| 45° | 41   | 34   |
| 55° | 14   | 14   |
| 65° | 10   | 9    |
| 75° | 5    | 5    |
| 85° | 1    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1267768

CATALOG NUMBER: P3AS17R259735DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3674.2 |
| 1°    | 3667.0 |
| 2°    | 3637.0 |
| 3°    | 3584.2 |
| 4°    | 3510.9 |
| 5°    | 3414.9 |
| 6°    | 3302.1 |
| 7°    | 3174.8 |
| 8°    | 3027.2 |
| 9°    | 2876.0 |
| 10°   | 2704.3 |
| 11°   | 2535.1 |
| 12°   | 2349.0 |
| 13°   | 2165.4 |
| 14°   | 1976.9 |
| 15°   | 1800.5 |
| 17.5° | 1396.0 |
| 20°   | 1059.9 |
| 22.5° | 795.8  |
| 25°   | 597.8  |
| 27.5° | 442.9  |
| 30°   | 325.3  |
| 32.5° | 235.3  |
| 35°   | 169.2  |
| 37.5° | 120.0  |
| 40°   | 84.0   |
| 42.5° | 57.6   |
| 45°   | 40.8   |
| 47.5° | 28.8   |
| 50°   | 21.6   |
| 52.5° | 16.8   |
| 55°   | 14.4   |
| 57.5° | 13.2   |
| 60°   | 10.8   |
| 62.5° | 9.6    |
| 65°   | 9.6    |
| 67.5° | 8.4    |
| 70°   | 7.2    |
| 72.5° | 6.0    |
| 75°   | 4.8    |
| 77.5° | 3.6    |
| 80°   | 2.4    |
| 82.5° | 2.4    |
| 85°   | 1.2    |
| 87.5° | 1.2    |



TEST NUMBER: P1267768

CATALOG NUMBER: P3AS17R259735DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)