

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266970

Luminaire Tested: P3AS09R209735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 346.0 lumens
Efficiency: N/A
Efficacy: 31.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266970
CATALOG NUMBER: P3AS09R209735DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1266970

CATALOG NUMBER: P3AS09R209735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	266207
5°	241998
10°	178843
15°	110625
20°	63169
25°	36075
30°	20231
35°	11002
40°	6040
45°	3318
50°	1944
55°	1415
60°	1316
65°	1193
70°	1090
75°	1101
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3318 cd/sqm



TEST NUMBER: P1266970
 CATALOG NUMBER: P3AS09R209735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	27.5
10°-20°	135.9	39.3
20°-30°	70.9	20.5
30°-40°	27.4	7.9
40°-50°	8.9	2.6
50°-60°	3.5	1.0
60°-70°	2.3	0.7
70°-80°	1.4	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	302.0	87.3
0°-40°	329.5	95.2
0°-60°	341.9	98.8
0°-90°	346.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	346.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1214	
5°	1099	95
15°	487	136
25°	149	71
35°	41	27
45°	11	9
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1266970
CATALOG NUMBER: P3AS09R209735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1214.0
1°	1211.7
2°	1197.3
3°	1175.2
4°	1141.1
5°	1099.4
6°	1049.9
7°	995.1
8°	931.6
9°	869.7
10°	803.2
12.5°	638.4
15°	487.3
17.5°	364.7
20°	270.7
22.5°	200.6
25°	149.1
27.5°	110.0
30°	79.9
32.5°	57.8
35°	41.1
37.5°	29.7
40°	21.1
42.5°	15.0
45°	10.7
47.5°	7.7
50°	5.7
52.5°	4.3
55°	3.7
57.5°	3.3
60°	3.0
62.5°	2.7
65°	2.3
67.5°	2.0
70°	1.7
72.5°	1.7
75°	1.3
77.5°	1.0
80°	0.7
82.5°	0.7
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)