

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266980

Luminaire Tested: P3AS09R209735DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209735DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 537.0 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266980

CATALOG NUMBER: P3AS09R209735DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1266980

CATALOG NUMBER: P3AS09R209735DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132818
5°	129275
10°	118925
15°	104677
20°	89771
25°	75416
30°	60971
35°	46391
40°	33005
45°	21801
50°	13509
55°	8869
60°	8070
65°	7420
70°	6988
75°	6354
80°	6061
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21801 cd/sqm

TEST NUMBER: P1266980

CATALOG NUMBER: P3AS09R209735DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	10.1
10°-20°	128.4	23.9
20°-30°	142.5	26.5
30°-40°	108.7	20.2
40°-50°	55.7	10.4
50°-60°	22.8	4.3
60°-70°	14.3	2.7
70°-80°	8.0	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	325.2	60.6
0°-40°	433.9	80.8
0°-60°	512.4	95.4
0°-90°	537.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	537.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	606	
5°	587	54
15°	461	128
25°	312	142
35°	173	109
45°	70	56
55°	23	23
65°	14	14
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1266980

CATALOG NUMBER: P3AS09R209735DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	605.7
1°	606.4
2°	603.7
3°	600.3
4°	594.8
5°	587.3
6°	578.5
7°	568.9
8°	558.7
9°	546.4
10°	534.1
12.5°	498.6
15°	461.1
17.5°	422.9
20°	384.7
22.5°	346.5
25°	311.7
27.5°	276.9
30°	240.8
32.5°	206.7
35°	173.3
37.5°	143.9
40°	115.3
42.5°	90.7
45°	70.3
47.5°	53.2
50°	39.6
52.5°	29.3
55°	23.2
57.5°	21.1
60°	18.4
62.5°	16.4
65°	14.3
67.5°	12.3
70°	10.9
72.5°	8.9
75°	7.5
77.5°	6.1
80°	4.8
82.5°	3.4
85°	2.0
87.5°	0.7
90°	0.0

(END OF REPORT)