

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266984

Luminaire Tested: P3AS09R209735DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266984
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209735DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 334.0 lumens
Efficiency: N/A
Efficacy: 30.1 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266984
CATALOG NUMBER: P3AS09R209735DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1266984
 CATALOG NUMBER: P3AS09R209735DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90				90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81				81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68				68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63				63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55				55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	59	52	48	68	58	52	48	57	52	48	57	52	48	56	51	48	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118784
5°	110786
10°	91938
15°	70307
20°	52761
25°	39728
30°	29372
35°	20532
40°	14084
45°	9768
50°	8392
55°	8258
60°	8640
65°	8665
70°	8848
75°	9150
80°	9976
85°	9812

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 11592 cd/sqm



TEST NUMBER: P1266984
 CATALOG NUMBER: P3AS09R209735DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	13.5
10°-20°	86.1	25.8
20°-30°	75.8	22.7
30°-40°	48.9	14.6
40°-50°	25.9	7.8
50°-60°	19.5	5.8
60°-70°	16.6	5.0
70°-80°	11.7	3.5
80°-90°	4.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	206.9	62.0
0°-40°	255.8	76.6
0°-60°	301.2	90.2
0°-90°	334.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	334.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	542	
5°	503	45
15°	310	86
25°	164	76
35°	77	49
45°	32	26
55°	22	19
65°	17	17
75°	11	12
85°	4	5
90°	0	



TEST NUMBER: P1266984
CATALOG NUMBER: P3AS09R209735DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	541.7
2.5°	530.8
5°	503.3
7.5°	461.0
10°	412.9
12.5°	359.8
15°	309.7
17.5°	264.4
20°	226.1
22.5°	193.7
25°	164.2
27.5°	138.6
30°	116.0
32.5°	95.4
35°	76.7
37.5°	61.9
40°	49.2
42.5°	39.3
45°	31.5
47.5°	27.5
50°	24.6
52.5°	22.6
55°	21.6
57.5°	20.6
60°	19.7
62.5°	17.7
65°	16.7
67.5°	15.7
70°	13.8
72.5°	12.8
75°	10.8
77.5°	9.8
80°	7.9
82.5°	6.9
85°	3.9
87.5°	2.0
90°	0.0

(END OF REPORT)