

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267788

Luminaire Tested: P3AS17R309735DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309735DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 774.0 lumens
Efficiency: N/A
Efficacy: 36.5 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267788
CATALOG NUMBER: P3AS17R309735DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1267788

CATALOG NUMBER: P3AS17R309735DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	264496
5°	256262
10°	230880
15°	190989
20°	147876
25°	110934
30°	80519
35°	53646
40°	32976
45°	19351
50°	11872
55°	9634
60°	8420
65°	6849
70°	6155
75°	6100
80°	4546
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19351 cd/sqm



TEST NUMBER: P1267788
 CATALOG NUMBER: P3AS17R309735DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.1	13.8
10°-20°	231.7	29.9
20°-30°	210.8	27.2
30°-40°	127.4	16.5
40°-50°	51.1	6.6
50°-60°	22.6	2.9
60°-70°	13.6	1.8
70°-80°	7.4	1.0
80°-90°	2.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	549.6	71.0
0°-40°	677.0	87.5
0°-60°	750.8	97.0
0°-90°	774.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	774.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1206	
5°	1164	107
15°	841	232
25°	458	211
35°	200	127
45°	62	51
55°	25	23
65°	13	14
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1267788

CATALOG NUMBER: P3AS17R309735DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1206.2
1°	1205.0
2°	1200.2
3°	1191.8
4°	1179.8
5°	1164.2
6°	1145.0
7°	1124.6
8°	1098.2
9°	1068.2
10°	1036.9
11°	1000.9
12°	962.5
13°	924.1
14°	882.1
15°	841.3
17.5°	734.5
20°	633.7
22.5°	540.1
25°	458.5
27.5°	384.1
30°	318.0
32.5°	256.8
35°	200.4
37.5°	153.6
40°	115.2
42.5°	84.0
45°	62.4
47.5°	46.8
50°	34.8
52.5°	27.6
55°	25.2
57.5°	21.6
60°	19.2
62.5°	15.6
65°	13.2
67.5°	12.0
70°	9.6
72.5°	8.4
75°	7.2
77.5°	6.0
80°	3.6
82.5°	2.4
85°	2.4
87.5°	1.2



TEST NUMBER: P1267788
CATALOG NUMBER: P3AS17R309735DE010 E3DL1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)