

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267002

Luminaire Tested: P3AS09R259735DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1267002  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R259735DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 268.0 lumens  
Efficiency: N/A  
Efficacy: 24.1 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267002  
CATALOG NUMBER: P3AS09R259735DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1267002  
 CATALOG NUMBER: P3AS09R259735DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	63701
5°	62183
10°	57625
15°	51306
20°	44104
25°	37478
30°	30866
35°	24039
40°	17290
45°	10978
50°	6482
55°	4473
60°	4079
65°	3788
70°	3398
75°	3135
80°	2904
85°	2516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10978 cd/sqm



TEST NUMBER: P1267002  
 CATALOG NUMBER: P3AS09R259735DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.2	9.8
10°-20°	62.7	23.4
20°-30°	70.9	26.5
30°-40°	56.1	20.9
40°-50°	28.3	10.6
50°-60°	11.4	4.2
60°-70°	7.2	2.7
70°-80°	4.0	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	159.8	59.7
0°-40°	215.9	80.6
0°-60°	255.6	95.4
0°-90°	268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	268.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	290	
5°	282	26
15°	226	63
25°	155	71
35°	90	56
45°	35	28
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1267002  
CATALOG NUMBER: P3AS09R259735DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	290.5
1°	290.5
2°	289.5
3°	287.8
4°	285.5
5°	282.5
6°	278.8
7°	274.4
8°	269.8
9°	264.4
10°	258.8
11°	252.4
12°	246.4
13°	239.4
14°	232.7
15°	226.0
17.5°	207.3
20°	189.0
22.5°	171.6
25°	154.9
27.5°	138.6
30°	121.9
32.5°	106.2
35°	89.8
37.5°	74.8
40°	60.4
42.5°	47.1
45°	35.4
47.5°	26.4
50°	19.0
52.5°	14.4
55°	11.7
57.5°	10.7
60°	9.3
62.5°	8.3
65°	7.3
67.5°	6.3
70°	5.3
72.5°	4.7
75°	3.7
77.5°	3.0
80°	2.3
82.5°	1.7
85°	1.0
87.5°	0.3



TEST NUMBER: P1267002  
CATALOG NUMBER: P3AS09R259735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)