

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267004

Luminaire Tested: P3AS09R259735DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259735DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 546.9 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267004
CATALOG NUMBER: P3AS09R259735DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1267004
 CATALOG NUMBER: P3AS09R259735DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130012
5°	126898
10°	117589
15°	104723
20°	90004
25°	76504
30°	62972
35°	49068
40°	35295
45°	22390
50°	13236
55°	9137
60°	8377
65°	7783
70°	6988
75°	6354
80°	6061
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22390 cd/sqm



TEST NUMBER: P1267004
 CATALOG NUMBER: P3AS09R259735DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	9.8
10°-20°	128.1	23.4
20°-30°	144.7	26.5
30°-40°	114.4	20.9
40°-50°	57.8	10.6
50°-60°	23.2	4.2
60°-70°	14.8	2.7
70°-80°	8.2	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.2	59.6
0°-40°	440.7	80.6
0°-60°	521.7	95.4
0°-90°	546.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	546.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	593	
5°	576	53
15°	461	128
25°	316	145
35°	183	114
45°	72	58
55°	24	23
65°	15	15
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1267004
CATALOG NUMBER: P3AS09R259735DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	592.9
1°	592.9
2°	590.8
3°	587.4
4°	582.6
5°	576.5
6°	569.0
7°	560.1
8°	550.6
9°	539.7
10°	528.1
11°	515.2
12°	502.9
13°	488.6
14°	475.0
15°	461.3
17.5°	423.2
20°	385.7
22.5°	350.3
25°	316.2
27.5°	282.8
30°	248.7
32.5°	216.7
35°	183.3
37.5°	152.6
40°	123.3
42.5°	96.1
45°	72.2
47.5°	53.8
50°	38.8
52.5°	29.3
55°	23.9
57.5°	21.8
60°	19.1
62.5°	17.0
65°	15.0
67.5°	12.9
70°	10.9
72.5°	9.5
75°	7.5
77.5°	6.1
80°	4.8
82.5°	3.4
85°	2.0
87.5°	0.7



TEST NUMBER: P1267004
CATALOG NUMBER: P3AS09R259735DE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)