

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267897

Luminaire Tested: P3AS17R509735DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509735DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1666.0 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267897

CATALOG NUMBER: P3AS17R509735DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267897

CATALOG NUMBER: P3AS17R509735DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	582190
5°	566695
10°	540783
15°	489583
20°	423560
25°	347439
30°	199575
35°	61998
40°	16660
45°	5830
50°	1399
55°	459
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5830 cd/sqm

TEST NUMBER: P1267897

CATALOG NUMBER: P3AS17R509735DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.1	14.5
10°-20°	597.5	35.9
20°-30°	628.1	37.7
30°-40°	179.8	10.8
40°-50°	17.6	1.1
50°-60°	1.4	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1466.7	88.0
0°-40°	1646.5	98.8
0°-60°	1665.5	100.0
0°-90°	1666.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1666.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2655	
5°	2574	241
15°	2157	598
25°	1436	628
35°	232	180
45°	19	18
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1267897

CATALOG NUMBER: P3AS17R509735DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2655.0
1°	2650.9
2°	2639.2
3°	2622.1
4°	2599.2
5°	2574.5
6°	2548.1
7°	2519.9
8°	2493.4
9°	2462.8
10°	2428.7
11°	2389.4
12°	2344.1
13°	2287.7
14°	2226.5
15°	2156.6
16°	2082.5
17°	2010.8
18°	1937.4
19°	1872.7
20°	1815.1
21°	1759.8
22°	1696.9
23°	1624.7
24°	1540.0
25°	1436.0
26°	1323.1
27°	1197.3
28°	1072.1
29°	936.9
30°	788.2
31°	648.9
32°	520.8
32.5°	464.9
33°	408.5
34°	313.3
35°	231.6
36°	169.9
37°	126.4
37.5°	109.3
38°	94.6
39°	73.5
40°	58.2
42.5°	32.9
45°	18.8



TEST NUMBER: P1267897

CATALOG NUMBER: P3AS17R509735DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	10.6
50°	4.1
52.5°	1.8
55°	1.2
57.5°	1.2
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)