

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267034

Luminaire Tested: P3AS09R309735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 271.9 lumens
Efficiency: N/A
Efficacy: 24.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267034

CATALOG NUMBER: P3AS09R309735DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1267034

CATALOG NUMBER: P3AS09R309735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	77	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64271
5°	62822
10°	58405
15°	51987
20°	44711
25°	37865
30°	31448
35°	24654
40°	17662
45°	11598
50°	6618
55°	4320
60°	4079
65°	3788
70°	3398
75°	3135
80°	2904
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11598 cd/sqm

TEST NUMBER: P1267034

CATALOG NUMBER: P3AS09R309735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	9.7
10°-20°	63.7	23.4
20°-30°	71.7	26.4
30°-40°	57.3	21.1
40°-50°	29.4	10.8
50°-60°	11.1	4.1
60°-70°	7.2	2.7
70°-80°	3.9	1.4
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	161.9	59.5
0°-40°	219.2	80.6
0°-60°	259.7	95.5
0°-90°	271.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	271.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	293	
5°	285	26
15°	229	64
25°	156	72
35°	92	57
45°	37	29
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1267034

CATALOG NUMBER: P3AS09R309735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	293.1
1°	293.1
2°	292.0
3°	290.4
4°	288.0
5°	285.4
6°	282.0
7°	277.7
8°	273.0
9°	267.7
10°	262.3
11°	256.3
12°	250.0
13°	243.3
14°	236.3
15°	229.0
17.5°	210.3
20°	191.6
22.5°	173.6
25°	156.5
27.5°	139.9
30°	124.2
32.5°	108.1
35°	92.1
37.5°	76.4
40°	61.7
42.5°	48.7
45°	37.4
47.5°	27.7
50°	19.4
52.5°	13.7
55°	11.3
57.5°	10.3
60°	9.3
62.5°	8.3
65°	7.3
67.5°	6.3
70°	5.3
72.5°	4.3
75°	3.7
77.5°	3.0
80°	2.3
82.5°	1.7
85°	1.0
87.5°	0.3



TEST NUMBER: P1267034

CATALOG NUMBER: P3AS09R309735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)