

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267973

Luminaire Tested: P3AS17R609735DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609735DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 872.1 lumens
Efficiency: N/A
Efficacy: 41.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267973

CATALOG NUMBER: P3AS17R609735DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267973

CATALOG NUMBER: P3AS17R609735DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	220991
5°	216024
10°	202245
15°	181454
20°	156044
25°	129032
30°	101940
35°	75703
40°	52126
45°	32717
50°	17978
55°	10552
60°	9473
65°	8094
70°	6924
75°	7117
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32717 cd/sqm

TEST NUMBER: P1267973

CATALOG NUMBER: P3AS17R609735DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	10.5
10°-20°	222.0	25.5
20°-30°	243.5	27.9
30°-40°	177.4	20.3
40°-50°	83.8	9.6
50°-60°	27.5	3.2
60°-70°	15.6	1.8
70°-80°	8.4	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.9	63.9
0°-40°	734.2	84.2
0°-60°	845.5	97.0
0°-90°	872.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	872.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1008	
5°	981	91
15°	799	222
25°	533	244
35°	283	177
45°	106	84
55°	28	27
65°	16	16
75°	8	8
85°	2	3
90°	0	

TEST NUMBER: P1267973

CATALOG NUMBER: P3AS17R609735DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1007.8
2.5°	1001.8
5°	981.4
7.5°	950.3
10°	908.3
12.5°	858.0
15°	799.3
17.5°	735.8
20°	668.7
22.5°	600.4
25°	533.3
27.5°	466.2
30°	402.6
32.5°	341.5
35°	282.8
37.5°	230.1
40°	182.1
42.5°	140.2
45°	105.5
47.5°	76.7
50°	52.7
52.5°	34.8
55°	27.6
57.5°	24.0
60°	21.6
62.5°	18.0
65°	15.6
67.5°	13.2
70°	10.8
72.5°	9.6
75°	8.4
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)