

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267062

Luminaire Tested: P3AS09R359735DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1267062  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R359735DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 270.0 lumens  
Efficiency: N/A  
Efficacy: 24.3 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267062  
CATALOG NUMBER: P3AS09R359735DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1267062  
 CATALOG NUMBER: P3AS09R359735DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	61684
5°	60378
10°	56534
15°	50738
20°	44151
25°	37623
30°	31524
35°	25110
40°	18148
45°	11474
50°	6277
55°	4320
60°	4079
65°	3788
70°	3654
75°	3135
80°	2904
85°	2516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11474 cd/sqm



TEST NUMBER: P1267062  
 CATALOG NUMBER: P3AS09R359735DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.5	9.5
10°-20°	62.2	23.0
20°-30°	71.3	26.4
30°-40°	58.2	21.6
40°-50°	29.3	10.9
50°-60°	10.9	4.0
60°-70°	7.3	2.7
70°-80°	4.1	1.5
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	159.0	58.9
0°-40°	217.2	80.5
0°-60°	257.4	95.3
0°-90°	270.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	270.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	281	
5°	274	26
15°	224	62
25°	156	71
35°	94	58
45°	37	29
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1267062  
CATALOG NUMBER: P3AS09R359735DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	281.3
1°	280.9
2°	280.3
3°	278.9
4°	276.9
5°	274.3
6°	270.9
7°	267.6
8°	263.2
9°	258.9
10°	253.9
11°	248.6
12°	242.9
13°	236.6
14°	229.9
15°	223.5
17.5°	206.5
20°	189.2
22.5°	171.5
25°	155.5
27.5°	139.8
30°	124.5
32.5°	109.1
35°	93.8
37.5°	78.4
40°	63.4
42.5°	49.4
45°	37.0
47.5°	26.7
50°	18.4
52.5°	13.3
55°	11.3
57.5°	10.3
60°	9.3
62.5°	8.3
65°	7.3
67.5°	6.3
70°	5.7
72.5°	4.7
75°	3.7
77.5°	3.0
80°	2.3
82.5°	1.7
85°	1.0
87.5°	0.7



TEST NUMBER: P1267062  
CATALOG NUMBER: P3AS09R359735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)