

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268014

Luminaire Tested: P3AS17R709735DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1268014  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R709735DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 592.0 lumens  
Efficiency: N/A  
Efficacy: 27.9 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268014  
CATALOG NUMBER: P3AS17R709735DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1268014  
 CATALOG NUMBER: P3AS17R709735DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114596
5°	113229
10°	109951
15°	105313
20°	98639
25°	89618
30°	77404
35°	61703
40°	44941
45°	29522
50°	13850
55°	4282
60°	4122
65°	3943
70°	3783
75°	3982
80°	3662
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29522 cd/sqm



TEST NUMBER: P1268014  
 CATALOG NUMBER: P3AS17R709735DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.4	8.2
10°-20°	129.8	21.9
20°-30°	168.7	28.5
30°-40°	143.2	24.2
40°-50°	73.8	12.5
50°-60°	14.2	2.4
60°-70°	7.7	1.3
70°-80°	4.7	0.8
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	347.0	58.6
0°-40°	490.2	82.8
0°-60°	578.2	97.7
0°-90°	592.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	592.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	523	
5°	514	48
15°	464	130
25°	370	169
35°	230	143
45°	95	74
55°	11	14
65°	8	8
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1268014  
CATALOG NUMBER: P3AS17R709735DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	522.6
2.5°	520.9
5°	514.4
7.5°	505.0
10°	493.8
12.5°	479.7
15°	463.9
17.5°	444.5
20°	422.7
22.5°	398.0
25°	370.4
27.5°	339.2
30°	305.7
32.5°	268.7
35°	230.5
37.5°	192.8
40°	157.0
42.5°	123.5
45°	95.2
47.5°	70.0
50°	40.6
52.5°	17.6
55°	11.2
57.5°	10.6
60°	9.4
62.5°	8.8
65°	7.6
67.5°	7.1
70°	5.9
72.5°	5.3
75°	4.7
77.5°	3.5
80°	2.9
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)