

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267063

Luminaire Tested: P3AS09R359735DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267063
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359735DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 552.0 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267063
CATALOG NUMBER: P3AS09R359735DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1267063
 CATALOG NUMBER: P3AS09R359735DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126086
5°	123420
10°	115585
15°	103746
20°	90261
25°	76916
30°	64415
35°	51317
40°	37098
45°	23475
50°	12793
55°	8869
60°	8377
65°	7783
70°	7437
75°	6354
80°	6061
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23475 cd/sqm



TEST NUMBER: P1267063
 CATALOG NUMBER: P3AS09R359735DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.2	9.5
10°-20°	127.2	23.0
20°-30°	145.7	26.4
30°-40°	118.9	21.5
40°-50°	60.0	10.9
50°-60°	22.3	4.0
60°-70°	15.0	2.7
70°-80°	8.3	1.5
80°-90°	2.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	325.1	58.9
0°-40°	444.0	80.4
0°-60°	526.3	95.3
0°-90°	552.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	552.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	575	
5°	561	52
15°	457	127
25°	318	146
35°	192	119
45°	76	60
55°	23	22
65°	15	15
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1267063
CATALOG NUMBER: P3AS09R359735DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	575.0
1°	574.3
2°	573.0
3°	570.3
4°	566.2
5°	560.7
6°	553.9
7°	547.1
8°	538.2
9°	529.3
10°	519.1
11°	508.2
12°	496.6
13°	483.6
14°	470.0
15°	457.0
17.5°	422.2
20°	386.8
22.5°	350.6
25°	317.9
27.5°	285.8
30°	254.4
32.5°	223.1
35°	191.7
37.5°	160.3
40°	129.6
42.5°	101.0
45°	75.7
47.5°	54.6
50°	37.5
52.5°	27.3
55°	23.2
57.5°	21.1
60°	19.1
62.5°	17.1
65°	15.0
67.5°	13.0
70°	11.6
72.5°	9.5
75°	7.5
77.5°	6.1
80°	4.8
82.5°	3.4
85°	2.0
87.5°	1.4



TEST NUMBER: P1267063
CATALOG NUMBER: P3AS09R359735DE010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)