

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267072

Luminaire Tested: P3AS09R359735DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359735DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 717.0 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267072
CATALOG NUMBER: P3AS09R359735DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1267072
 CATALOG NUMBER: P3AS09R359735DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	67	67	67	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	361616
5°	347545
10°	302822
15°	231942
20°	155180
25°	93901
30°	53882
35°	30115
40°	16001
45°	8249
50°	3957
55°	3135
60°	2982
65°	2491
70°	2629
75°	2288
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8249 cd/sqm



TEST NUMBER: P1267072
 CATALOG NUMBER: P3AS09R359735DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.7	20.0
10°-20°	278.4	38.8
20°-30°	182.3	25.4
30°-40°	73.9	10.3
40°-50°	22.2	3.1
50°-60°	7.5	1.1
60°-70°	5.1	0.7
70°-80°	2.9	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	604.3	84.3
0°-40°	678.2	94.6
0°-60°	708.0	98.7
0°-90°	717.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	717.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1649	
5°	1579	144
15°	1022	278
25°	388	182
35°	112	74
45°	27	22
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1267072
CATALOG NUMBER: P3AS09R359735DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1649.1
1°	1646.4
2°	1638.9
3°	1623.9
4°	1606.2
5°	1578.9
6°	1544.8
7°	1506.6
8°	1463.6
9°	1414.5
10°	1360.0
11°	1299.3
12°	1235.8
13°	1164.9
14°	1097.4
15°	1021.7
17.5°	838.2
20°	665.0
22.5°	511.5
25°	388.1
27.5°	289.2
30°	212.8
32.5°	156.2
35°	112.5
37.5°	79.8
40°	55.9
42.5°	38.9
45°	26.6
47.5°	17.7
50°	11.6
52.5°	8.9
55°	8.2
57.5°	7.5
60°	6.8
62.5°	6.1
65°	4.8
67.5°	4.1
70°	4.1
72.5°	3.4
75°	2.7
77.5°	2.0
80°	2.0
82.5°	1.4
85°	0.7
87.5°	0.7



TEST NUMBER: P1267072
CATALOG NUMBER: P3AS09R359735DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)