

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268018

Luminaire Tested: P3AS17R709735DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268018
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709735DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 862.0 lumens
Efficiency: N/A
Efficacy: 40.7 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268018

CATALOG NUMBER: P3AS17R709735DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1268018

CATALOG NUMBER: P3AS17R709735DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	88	83		98	92	87	83		89	85	81		87	83	80		84	81	79
4	95	86	80	76		93	85	80	75		83	78	74		81	77	73		79	76	73
5	89	80	74	69		88	79	73	69		78	72	68		76	71	68		74	70	67
6	85	75	68	64		83	74	68	64		73	67	63		71	66	63		70	65	62
7	80	70	64	59		79	69	63	59		68	62	58		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	62	55	51		71	61	55	51		60	55	51		59	54	51		58	54	50
10	69	58	52	48		67	58	52	48		57	51	48		56	51	48		55	51	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202199
5°	198481
10°	187149
15°	169853
20°	148576
25°	125330
30°	102623
35°	79612
40°	56964
45°	36066
50°	18012
55°	11010
60°	9473
65°	8717
70°	7694
75°	7117
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36066 cd/sqm

TEST NUMBER: P1268018

CATALOG NUMBER: P3AS17R709735DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.1	9.8
10°-20°	208.2	24.2
20°-30°	237.1	27.5
30°-40°	185.4	21.5
40°-50°	91.1	10.6
50°-60°	28.0	3.3
60°-70°	16.6	1.9
70°-80°	8.9	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.4	61.4
0°-40°	714.8	82.9
0°-60°	833.9	96.7
0°-90°	862.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	862.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	922	
5°	902	84
15°	748	208
25°	518	237
35°	297	185
45°	116	91
55°	29	28
65°	17	17
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1268018

CATALOG NUMBER: P3AS17R709735DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	922.1
2.5°	917.3
5°	901.7
7.5°	876.5
10°	840.5
12.5°	798.6
15°	748.2
17.5°	694.2
20°	636.7
22.5°	576.7
25°	518.0
27.5°	460.4
30°	405.3
32.5°	350.1
35°	297.4
37.5°	247.0
40°	199.0
42.5°	154.7
45°	116.3
47.5°	81.5
50°	52.8
52.5°	34.8
55°	28.8
57.5°	25.2
60°	21.6
62.5°	19.2
65°	16.8
67.5°	14.4
70°	12.0
72.5°	9.6
75°	8.4
77.5°	7.2
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)