

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267105

Luminaire Tested: P3AS09R409735DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409735DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 501.0 lumens
Efficiency: N/A
Efficacy: 45.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267105

CATALOG NUMBER: P3AS09R409735DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267105

CATALOG NUMBER: P3AS09R409735DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155996
5°	152850
10°	142304
15°	124042
20°	99969
25°	74932
30°	52666
35°	34506
40°	20896
45°	12466
50°	7437
55°	6002
60°	5394
65°	4618
70°	4360
75°	3474
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12466 cd/sqm

TEST NUMBER: P1267105

CATALOG NUMBER: P3AS09R409735DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.5	12.9
10°-20°	150.5	30.0
20°-30°	141.8	28.3
30°-40°	82.0	16.4
40°-50°	32.7	6.5
50°-60°	14.5	2.9
60°-70°	8.9	1.8
70°-80°	4.7	0.9
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	356.8	71.2
0°-40°	438.8	87.6
0°-60°	485.9	97.0
0°-90°	501.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	501.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	711	
5°	694	64
15°	546	150
25°	310	142
35°	129	82
45°	40	33
55°	16	14
65°	9	9
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1267105

CATALOG NUMBER: P3AS09R409735DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	711.4
2.5°	707.3
5°	694.4
7.5°	670.5
10°	639.1
12.5°	596.8
15°	546.4
17.5°	489.7
20°	428.4
22.5°	367.0
25°	309.7
27.5°	256.5
30°	208.0
32.5°	165.7
35°	128.9
37.5°	97.5
40°	73.0
42.5°	54.6
45°	40.2
47.5°	29.3
50°	21.8
52.5°	17.7
55°	15.7
57.5°	14.3
60°	12.3
62.5°	10.2
65°	8.9
67.5°	7.5
70°	6.8
72.5°	5.5
75°	4.1
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)