

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267124

Luminaire Tested: P3AS09R459735DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1267124  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R459735DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 592.0 lumens  
Efficiency: N/A  
Efficacy: 53.3 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267124

CATALOG NUMBER: P3AS09R459735DE010 E3DLD1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1267124

CATALOG NUMBER: P3AS09R459735DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 97  | 96  |  | 96  |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  |  | 92  | 89  | 86  |  | 89  |
| 3   | 99  | 92  | 86  | 82  | 97  | 90  | 85  | 81  | 88  | 83  | 80  |  | 85  | 81  | 78  |  | 83  |
| 4   | 94  | 85  | 78  | 74  | 92  | 84  | 78  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 5   | 88  | 79  | 72  | 67  | 86  | 78  | 71  | 67  | 76  | 70  | 66  |  | 74  | 69  | 65  |  | 72  |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 66  | 61  | 71  | 65  | 61  |  | 69  | 64  | 60  |  | 68  |
| 7   | 78  | 68  | 61  | 57  | 77  | 67  | 61  | 56  | 66  | 60  | 56  |  | 65  | 60  | 56  |  | 64  |
| 8   | 74  | 64  | 57  | 52  | 73  | 63  | 57  | 52  | 62  | 56  | 52  |  | 61  | 56  | 52  |  | 60  |
| 9   | 70  | 60  | 53  | 49  | 69  | 59  | 53  | 49  | 58  | 52  | 48  |  | 57  | 52  | 48  |  | 56  |
| 10  | 67  | 56  | 50  | 45  | 66  | 56  | 49  | 45  | 55  | 49  | 45  |  | 54  | 49  | 45  |  | 53  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 125516 |
| 5°  | 123288 |
| 10° | 116676 |
| 15° | 106402 |
| 20° | 94088  |
| 25° | 81706  |
| 30° | 70137  |
| 35° | 58437  |
| 40° | 43539  |
| 45° | 26669  |
| 50° | 12349  |
| 55° | 9634   |
| 60° | 9254   |
| 65° | 8509   |
| 70° | 7886   |
| 75° | 7540   |
| 80° | 6945   |
| 85° | 5032   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26669 cd/sqm

TEST NUMBER: P1267124

CATALOG NUMBER: P3AS09R459735DE010 E3DLD1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 52.3   | 8.8       |
| 10°-20°   | 130.5  | 22.0      |
| 20°-30°   | 155.0  | 26.2      |
| 30°-40°   | 134.7  | 22.8      |
| 40°-50°   | 67.6   | 11.4      |
| 50°-60°   | 23.5   | 4.0       |
| 60°-70°   | 16.4   | 2.8       |
| 70°-80°   | 9.2    | 1.6       |
| 80°-90°   | 2.8    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 337.9  | 57.1      |
| 0°-40°    | 472.6  | 79.8      |
| 0°-60°    | 563.6  | 95.2      |
| 0°-90°    | 592.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 592.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 572 |      |
| 5°  | 560 | 52   |
| 15° | 469 | 130  |
| 25° | 338 | 155  |
| 35° | 218 | 135  |
| 45° | 86  | 68   |
| 55° | 25  | 23   |
| 65° | 16  | 16   |
| 75° | 9   | 9    |
| 85° | 2   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1267124

CATALOG NUMBER: P3AS09R459735DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 572.4 |
| 2.5°  | 569.7 |
| 5°    | 560.1 |
| 7.5°  | 545.1 |
| 10°   | 524.0 |
| 12.5° | 498.0 |
| 15°   | 468.7 |
| 17.5° | 436.0 |
| 20°   | 403.2 |
| 22.5° | 369.8 |
| 25°   | 337.7 |
| 27.5° | 307.0 |
| 30°   | 277.0 |
| 32.5° | 248.3 |
| 35°   | 218.3 |
| 37.5° | 186.3 |
| 40°   | 152.1 |
| 42.5° | 118.7 |
| 45°   | 86.0  |
| 47.5° | 56.6  |
| 50°   | 36.2  |
| 52.5° | 28.0  |
| 55°   | 25.2  |
| 57.5° | 23.2  |
| 60°   | 21.1  |
| 62.5° | 19.1  |
| 65°   | 16.4  |
| 67.5° | 14.3  |
| 70°   | 12.3  |
| 72.5° | 10.2  |
| 75°   | 8.9   |
| 77.5° | 6.8   |
| 80°   | 5.5   |
| 82.5° | 4.1   |
| 85°   | 2.0   |
| 87.5° | 1.4   |
| 90°   | 0.0   |

(END OF REPORT)