

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268109

Luminaire Tested: P3AS20R209735D010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1268109  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R209735D010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 608.0 lumens  
Efficiency: N/A  
Efficacy: 21.1 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268109

CATALOG NUMBER: P3AS20R209735D010 E3DLD1GPH

### Luminous Intensity Polar Plot



TEST NUMBER: P1268109

CATALOG NUMBER: P3AS20R209735D010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 90  |
| 3   | 100 | 93  | 87  | 82  | 98  | 91  | 86  | 82  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 84  |
| 4   | 94  | 86  | 79  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 71  | 67  |  | 75  | 70  | 67  |  | 73  |
| 6   | 84  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 66  | 62  |  | 70  | 65  | 62  |  | 69  |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 62  | 58  | 67  | 62  | 58  |  | 66  | 61  | 57  |  | 65  |
| 8   | 75  | 65  | 59  | 54  | 74  | 64  | 58  | 54  | 63  | 58  | 54  |  | 62  | 57  | 53  |  | 61  |
| 9   | 72  | 61  | 55  | 50  | 70  | 61  | 55  | 50  | 60  | 54  | 50  |  | 59  | 54  | 50  |  | 58  |
| 10  | 68  | 58  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 51  | 47  |  | 56  | 50  | 47  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 150383 |
| 5°  | 146379 |
| 10° | 134645 |
| 15° | 118525 |
| 20° | 101649 |
| 25° | 85408  |
| 30° | 69023  |
| 35° | 52521  |
| 40° | 37356  |
| 45° | 24685  |
| 50° | 15283  |
| 55° | 10055  |
| 60° | 9166   |
| 65° | 8406   |
| 70° | 7950   |
| 75° | 7202   |
| 80° | 6819   |
| 85° | 5787   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24685 cd/sqm

TEST NUMBER: P1268109

CATALOG NUMBER: P3AS20R209735D010 E3DLD1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 61.5   | 10.1      |
| 10°-20°   | 145.3  | 23.9      |
| 20°-30°   | 161.3  | 26.5      |
| 30°-40°   | 123.1  | 20.2      |
| 40°-50°   | 63.0   | 10.4      |
| 50°-60°   | 25.9   | 4.3       |
| 60°-70°   | 16.1   | 2.7       |
| 70°-80°   | 9.1    | 1.5       |
| 80°-90°   | 2.6    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 368.2  | 60.6      |
| 0°-40°    | 491.3  | 80.8      |
| 0°-60°    | 580.2  | 95.4      |
| 0°-90°    | 608.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 608.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 686 |      |
| 5°  | 665 | 62   |
| 15° | 522 | 145  |
| 25° | 353 | 161  |
| 35° | 196 | 123  |
| 45° | 80  | 63   |
| 55° | 26  | 26   |
| 65° | 16  | 16   |
| 75° | 8   | 9    |
| 85° | 2   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1268109

CATALOG NUMBER: P3AS20R209735D010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 685.8 |
| 1°    | 686.6 |
| 2°    | 683.5 |
| 3°    | 679.7 |
| 4°    | 673.5 |
| 5°    | 665.0 |
| 6°    | 654.9 |
| 7°    | 644.1 |
| 8°    | 632.5 |
| 9°    | 618.6 |
| 10°   | 604.7 |
| 12.5° | 564.6 |
| 15°   | 522.1 |
| 17.5° | 478.8 |
| 20°   | 435.6 |
| 22.5° | 392.3 |
| 25°   | 353.0 |
| 27.5° | 313.6 |
| 30°   | 272.6 |
| 32.5° | 234.0 |
| 35°   | 196.2 |
| 37.5° | 163.0 |
| 40°   | 130.5 |
| 42.5° | 102.7 |
| 45°   | 79.6  |
| 47.5° | 60.2  |
| 50°   | 44.8  |
| 52.5° | 33.2  |
| 55°   | 26.3  |
| 57.5° | 23.9  |
| 60°   | 20.9  |
| 62.5° | 18.5  |
| 65°   | 16.2  |
| 67.5° | 13.9  |
| 70°   | 12.4  |
| 72.5° | 10.0  |
| 75°   | 8.5   |
| 77.5° | 7.0   |
| 80°   | 5.4   |
| 82.5° | 3.9   |
| 85°   | 2.3   |
| 87.5° | 0.8   |
| 90°   | 0.0   |

(END OF REPORT)