

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267126

Luminaire Tested: P3AS09R459735DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459735DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 492.0 lumens
Efficiency: N/A
Efficacy: 44.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267126
CATALOG NUMBER: P3AS09R459735DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1267126
 CATALOG NUMBER: P3AS09R459735DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64				64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60				60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56				56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146545
5°	143209
10°	132106
15°	114870
20°	94368
25°	73432
30°	54211
35°	38146
40°	23816
45°	12901
50°	6993
55°	6002
60°	5394
65°	4618
70°	3911
75°	4067
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12901 cd/sqm



TEST NUMBER: P1267126
 CATALOG NUMBER: P3AS09R459735DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	12.2
10°-20°	139.9	28.4
20°-30°	138.9	28.2
30°-40°	89.4	18.2
40°-50°	34.5	7.0
50°-60°	14.0	2.8
60°-70°	8.8	1.8
70°-80°	4.8	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	339.0	68.9
0°-40°	428.4	87.1
0°-60°	476.9	96.9
0°-90°	492.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	492.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	668	
5°	651	60
15°	506	140
25°	304	139
35°	142	89
45°	42	34
55°	16	14
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1267126
CATALOG NUMBER: P3AS09R459735DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	668.3
2.5°	664.9
5°	650.6
7.5°	626.0
10°	593.3
12.5°	552.4
15°	506.0
17.5°	455.5
20°	404.4
22.5°	352.6
25°	303.5
27.5°	257.1
30°	214.1
32.5°	176.6
35°	142.5
37.5°	111.8
40°	83.2
42.5°	60.0
45°	41.6
47.5°	28.0
50°	20.5
52.5°	17.0
55°	15.7
57.5°	13.6
60°	12.3
62.5°	10.2
65°	8.9
67.5°	7.5
70°	6.1
72.5°	5.5
75°	4.8
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)