

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267128

Luminaire Tested: P3AS09R459735DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459735DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 492.0 lumens
Efficiency: N/A
Efficacy: 44.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267128

CATALOG NUMBER: P3AS09R459735DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1267128

CATALOG NUMBER: P3AS09R459735DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	106	103		104	102	100		100	99	97		97	96	94
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	102	95	90	85		100	93	89	85		91	87	83		88	85	82		86	83	81
4	96	88	83	78		94	87	82	78		85	81	77		83	79	76		81	78	75
5	91	83	77	72		90	82	76	72		80	75	71		78	74	71		77	73	70
6	87	78	72	67		85	77	71	67		75	70	66		74	69	66		73	69	66
7	83	73	67	63		81	72	67	63		71	66	62		70	65	62		69	65	61
8	79	69	63	59		77	68	63	59		67	62	58		66	62	58		65	61	58
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	55	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146545
5°	143209
10°	132106
15°	114870
20°	94368
25°	73432
30°	54211
35°	38146
40°	23816
45°	12901
50°	6993
55°	6002
60°	5394
65°	4618
70°	3911
75°	4067
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12901 cd/sqm

TEST NUMBER: P1267128

CATALOG NUMBER: P3AS09R459735DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	12.2
10°-20°	139.9	28.4
20°-30°	138.9	28.2
30°-40°	89.4	18.2
40°-50°	34.5	7.0
50°-60°	14.0	2.8
60°-70°	8.8	1.8
70°-80°	4.8	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	339.0	68.9
0°-40°	428.4	87.1
0°-60°	476.9	96.9
0°-90°	492.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	492.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	668	
5°	651	60
15°	506	140
25°	304	139
35°	142	89
45°	42	34
55°	16	14
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1267128

CATALOG NUMBER: P3AS09R459735DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	668.3
2.5°	664.9
5°	650.6
7.5°	626.0
10°	593.3
12.5°	552.4
15°	506.0
17.5°	455.5
20°	404.4
22.5°	352.6
25°	303.5
27.5°	257.1
30°	214.1
32.5°	176.6
35°	142.5
37.5°	111.8
40°	83.2
42.5°	60.0
45°	41.6
47.5°	28.0
50°	20.5
52.5°	17.0
55°	15.7
57.5°	13.6
60°	12.3
62.5°	10.2
65°	8.9
67.5°	7.5
70°	6.1
72.5°	5.5
75°	4.8
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)