

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267141

Luminaire Tested: P3AS09R509735DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509735DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 947.0 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267141

CATALOG NUMBER: P3AS09R509735DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267141

CATALOG NUMBER: P3AS09R509735DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	330938
5°	322121
10°	307409
15°	278299
20°	240774
25°	197479
30°	113435
35°	35228
40°	9475
45°	3318
50°	785
55°	268
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3318 cd/sqm

TEST NUMBER: P1267141

CATALOG NUMBER: P3AS09R509735DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.1	14.5
10°-20°	339.7	35.9
20°-30°	357.0	37.7
30°-40°	102.2	10.8
40°-50°	10.0	1.1
50°-60°	0.8	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.7	88.0
0°-40°	935.9	98.8
0°-60°	946.7	100.0
0°-90°	947.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1509	
5°	1463	137
15°	1226	340
25°	816	357
35°	132	102
45°	11	10
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1267141

CATALOG NUMBER: P3AS09R509735DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1509.2
1°	1506.9
2°	1500.2
3°	1490.5
4°	1477.5
5°	1463.4
6°	1448.4
7°	1432.4
8°	1417.3
9°	1399.9
10°	1380.6
11°	1358.2
12°	1332.5
13°	1300.4
14°	1265.6
15°	1225.9
16°	1183.8
17°	1143.0
18°	1101.2
19°	1064.5
20°	1031.8
21°	1000.3
22°	964.6
23°	923.5
24°	875.4
25°	816.2
26°	752.1
27°	680.6
28°	609.4
29°	532.6
30°	448.0
31°	368.9
32°	296.0
32.5°	264.3
33°	232.2
34°	178.1
35°	131.6
36°	96.6
37°	71.8
37.5°	62.1
38°	53.8
39°	41.8
40°	33.1
42.5°	18.7
45°	10.7

TEST NUMBER: P1267141

CATALOG NUMBER: P3AS09R509735DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.0
50°	2.3
52.5°	1.0
55°	0.7
57.5°	0.7
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)