

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267150

Luminaire Tested: P3AS09R509735DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509735DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 597.0 lumens
Efficiency: N/A
Efficacy: 53.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267150
CATALOG NUMBER: P3AS09R509735DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1267150
 CATALOG NUMBER: P3AS09R509735DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121328
5°	119546
10°	114249
15°	105812
20°	95092
25°	83594
30°	71074
35°	57634
40°	43310
45°	27879
50°	13236
55°	10437
60°	9868
65°	9184
70°	8271
75°	7540
80°	6945
85°	6793

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27879 cd/sqm



TEST NUMBER: P1267150
 CATALOG NUMBER: P3AS09R509735DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	8.5
10°-20°	129.9	21.8
20°-30°	157.9	26.4
30°-40°	133.9	22.4
40°-50°	69.5	11.6
50°-60°	25.1	4.2
60°-70°	17.4	2.9
70°-80°	9.4	1.6
80°-90°	3.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.7	56.7
0°-40°	472.6	79.2
0°-60°	567.3	95.0
0°-90°	597.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	597.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	553	
5°	543	51
15°	466	130
25°	346	158
35°	215	134
45°	90	70
55°	27	25
65°	18	17
75°	9	9
85°	3	3
90°	0	



TEST NUMBER: P1267150
CATALOG NUMBER: P3AS09R509735DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	553.3
2.5°	551.2
5°	543.1
7.5°	530.8
10°	513.1
12.5°	490.6
15°	466.1
17.5°	438.1
20°	407.5
22.5°	376.1
25°	345.5
27.5°	313.4
30°	280.7
32.5°	248.0
35°	215.3
37.5°	183.3
40°	151.3
42.5°	120.6
45°	89.9
47.5°	60.0
50°	38.8
52.5°	30.0
55°	27.3
57.5°	24.5
60°	22.5
62.5°	19.8
65°	17.7
67.5°	15.0
70°	12.9
72.5°	10.9
75°	8.9
77.5°	6.8
80°	5.5
82.5°	4.1
85°	2.7
87.5°	1.4
90°	0.0

(END OF REPORT)