

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268168

Luminaire Tested: P3AS20R309735D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309735D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 629.0 lumens
Efficiency: N/A
Efficacy: 21.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268168

CATALOG NUMBER: P3AS20R309735D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268168

CATALOG NUMBER: P3AS20R309735D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148607
5°	145256
10°	135090
15°	120205
20°	103376
25°	87586
30°	72695
35°	57018
40°	40877
45°	26793
50°	15283
55°	10016
60°	9473
65°	8821
70°	7886
75°	7202
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26793 cd/sqm

TEST NUMBER: P1268168

CATALOG NUMBER: P3AS20R309735D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.3	9.7
10°-20°	147.2	23.4
20°-30°	165.9	26.4
30°-40°	132.5	21.1
40°-50°	68.1	10.8
50°-60°	25.6	4.1
60°-70°	16.8	2.7
70°-80°	9.0	1.4
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	374.4	59.5
0°-40°	506.8	80.6
0°-60°	600.5	95.5
0°-90°	629.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	629.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	678	
5°	660	61
15°	530	147
25°	362	166
35°	213	132
45°	86	68
55°	26	26
65°	17	17
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1268168

CATALOG NUMBER: P3AS20R309735D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	677.7
1°	677.7
2°	675.4
3°	671.5
4°	666.1
5°	659.9
6°	652.2
7°	642.2
8°	631.4
9°	619.0
10°	606.7
11°	592.8
12°	578.1
13°	562.7
14°	546.5
15°	529.5
17.5°	486.3
20°	443.0
22.5°	401.4
25°	362.0
27.5°	323.4
30°	287.1
32.5°	250.1
35°	213.0
37.5°	176.8
40°	142.8
42.5°	112.7
45°	86.4
47.5°	64.1
50°	44.8
52.5°	31.6
55°	26.2
57.5°	23.9
60°	21.6
62.5°	19.3
65°	17.0
67.5°	14.7
70°	12.3
72.5°	10.0
75°	8.5
77.5°	6.9
80°	5.4
82.5°	3.9
85°	2.3
87.5°	0.8



TEST NUMBER: P1268168

CATALOG NUMBER: P3AS20R309735D010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)