

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267187

Luminaire Tested: P3AS09R559735DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559735DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 743.0 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267187
CATALOG NUMBER: P3AS09R559735DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1267187
 CATALOG NUMBER: P3AS09R559735DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93				93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87				87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81				81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75				75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66				66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	204019
5°	201959
10°	195031
15°	180273
20°	155554
25°	122862
30°	87153
35°	56189
40°	33749
45°	19010
50°	10234
55°	3632
60°	3289
65°	3165
70°	3077
75°	2881
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19010 cd/sqm



TEST NUMBER: P1267187
 CATALOG NUMBER: P3AS09R559735DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.3	11.6
10°-20°	219.6	29.6
20°-30°	230.1	31.0
30°-40°	134.3	18.1
40°-50°	50.2	6.8
50°-60°	11.8	1.6
60°-70°	6.1	0.8
70°-80°	3.6	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.0	72.1
0°-40°	670.2	90.2
0°-60°	732.3	98.6
0°-90°	743.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	743.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	930	
5°	918	86
15°	794	220
25°	508	230
35°	210	134
45°	61	50
55°	10	12
65°	6	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1267187
CATALOG NUMBER: P3AS09R559735DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	930.4
2.5°	927.7
5°	917.5
7.5°	901.1
10°	875.9
12.5°	840.4
15°	794.1
17.5°	735.5
20°	666.6
22.5°	589.6
25°	507.8
27.5°	424.0
30°	344.2
32.5°	272.0
35°	209.9
37.5°	159.5
40°	117.9
42.5°	84.5
45°	61.3
47.5°	44.3
50°	30.0
52.5°	17.0
55°	9.5
57.5°	8.2
60°	7.5
62.5°	6.8
65°	6.1
67.5°	5.5
70°	4.8
72.5°	4.1
75°	3.4
77.5°	2.7
80°	2.0
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)