

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267195

Luminaire Tested: P3AS09R609735DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609735DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 817.0 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267195

CATALOG NUMBER: P3AS09R609735DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1267195

CATALOG NUMBER: P3AS09R609735DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214062
5°	202091
10°	196834
15°	192328
20°	178819
25°	159856
30°	122120
35°	70510
40°	27366
45°	11412
50°	2524
55°	382
60°	307
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11412 cd/sqm

TEST NUMBER: P1267195

CATALOG NUMBER: P3AS09R609735DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	10.6
10°-20°	236.0	28.9
20°-30°	295.6	36.2
30°-40°	165.2	20.2
40°-50°	31.4	3.8
50°-60°	1.6	0.2
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	618.2	75.7
0°-40°	783.5	95.9
0°-60°	816.5	99.9
0°-90°	817.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	817.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	976	
5°	918	87
15°	847	236
25°	661	296
35°	263	165
45°	37	31
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1267195

CATALOG NUMBER: P3AS09R609735DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	976.2
1°	972.2
2°	959.5
3°	944.5
4°	930.4
5°	918.1
6°	908.7
7°	900.7
8°	894.7
9°	889.0
10°	884.0
11°	879.0
12°	873.3
13°	866.3
14°	857.9
15°	847.2
16°	834.2
17°	819.5
18°	802.8
19°	783.7
20°	766.3
21°	747.6
22°	728.2
23°	707.8
24°	685.5
25°	660.7
26°	631.6
27°	599.2
28°	562.8
29°	524.0
30°	482.3
31°	440.1
32°	396.7
32.5°	373.0
33°	351.6
34°	307.1
35°	263.4
36°	223.9
37°	182.1
37.5°	163.1
38°	144.4
39°	116.3
40°	95.6
42.5°	58.2
45°	36.8

TEST NUMBER: P1267195

CATALOG NUMBER: P3AS09R609735DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	20.4
50°	7.4
52.5°	1.7
55°	1.0
57.5°	0.7
60°	0.7
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)