

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267198

Luminaire Tested: P3AS09R609735DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609735DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 817.0 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267198
CATALOG NUMBER: P3AS09R609735DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1267198
 CATALOG NUMBER: P3AS09R609735DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214062
5°	202091
10°	196834
15°	192328
20°	178819
25°	159856
30°	122120
35°	70510
40°	27366
45°	11412
50°	2524
55°	382
60°	307
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11412 cd/sqm



TEST NUMBER: P1267198
 CATALOG NUMBER: P3AS09R609735DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	10.6
10°-20°	236.0	28.9
20°-30°	295.6	36.2
30°-40°	165.2	20.2
40°-50°	31.4	3.8
50°-60°	1.6	0.2
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	618.2	75.7
0°-40°	783.5	95.9
0°-60°	816.5	99.9
0°-90°	817.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	817.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	976	
5°	918	87
15°	847	236
25°	661	296
35°	263	165
45°	37	31
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1267198
CATALOG NUMBER: P3AS09R609735DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	976.2
1°	972.2
2°	959.5
3°	944.5
4°	930.4
5°	918.1
6°	908.7
7°	900.7
8°	894.7
9°	889.0
10°	884.0
11°	879.0
12°	873.3
13°	866.3
14°	857.9
15°	847.2
16°	834.2
17°	819.5
18°	802.8
19°	783.7
20°	766.3
21°	747.6
22°	728.2
23°	707.8
24°	685.5
25°	660.7
26°	631.6
27°	599.2
28°	562.8
29°	524.0
30°	482.3
31°	440.1
32°	396.7
32.5°	373.0
33°	351.6
34°	307.1
35°	263.4
36°	223.9
37°	182.1
37.5°	163.1
38°	144.4
39°	116.3
40°	95.6
42.5°	58.2
45°	36.8



TEST NUMBER: P1267198
CATALOG NUMBER: P3AS09R609735DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	20.4
50°	7.4
52.5°	1.7
55°	1.0
57.5°	0.7
60°	0.7
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)