

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267237

Luminaire Tested: P3AS09R659735DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267237
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659735DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 537.0 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267237
CATALOG NUMBER: P3AS09R659735DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1267237
 CATALOG NUMBER: P3AS09R659735DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95563
5°	94277
10°	91114
15°	85926
20°	79247
25°	71956
30°	63731
35°	54234
40°	43138
45°	30453
50°	17671
55°	9634
60°	8991
65°	8146
70°	7437
75°	6947
80°	6061
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30453 cd/sqm



TEST NUMBER: P1267237
 CATALOG NUMBER: P3AS09R659735DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.3	7.5
10°-20°	105.9	19.7
20°-30°	136.1	25.3
30°-40°	125.9	23.4
40°-50°	76.0	14.1
50°-60°	25.9	4.8
60°-70°	15.6	2.9
70°-80°	8.8	1.6
80°-90°	2.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	282.3	52.6
0°-40°	408.2	76.0
0°-60°	510.1	95.0
0°-90°	537.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	537.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	436	
5°	428	40
15°	378	106
25°	297	136
35°	203	126
45°	98	76
55°	25	26
65°	16	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1267237
CATALOG NUMBER: P3AS09R659735DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	435.8
2.5°	433.7
5°	428.3
7.5°	420.1
10°	409.2
12.5°	395.6
15°	378.5
17.5°	360.1
20°	339.6
22.5°	318.5
25°	297.4
27.5°	274.8
30°	251.7
32.5°	228.5
35°	202.6
37.5°	177.3
40°	150.7
42.5°	124.1
45°	98.2
47.5°	74.3
50°	51.8
52.5°	32.7
55°	25.2
57.5°	22.5
60°	20.5
62.5°	17.7
65°	15.7
67.5°	13.6
70°	11.6
72.5°	10.2
75°	8.2
77.5°	6.8
80°	4.8
82.5°	3.4
85°	2.0
87.5°	1.4
90°	0.0

(END OF REPORT)