

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268247

Luminaire Tested: P3AS20R459735D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459735D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 863.0 lumens
Efficiency: N/A
Efficacy: 30.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268247

CATALOG NUMBER: P3AS20R459735D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268247

CATALOG NUMBER: P3AS20R459735D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	324097
5°	316486
10°	290932
15°	246517
20°	191257
25°	133701
30°	84215
35°	49577
40°	28053
45°	13645
50°	4742
55°	3823
60°	3728
65°	3580
70°	3462
75°	3304
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13645 cd/sqm

TEST NUMBER: P1268247

CATALOG NUMBER: P3AS20R459735D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.1	15.4
10°-20°	298.2	34.6
20°-30°	253.2	29.3
30°-40°	120.8	14.0
40°-50°	36.4	4.2
50°-60°	9.2	1.1
60°-70°	6.9	0.8
70°-80°	4.1	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	684.5	79.3
0°-40°	805.3	93.3
0°-60°	850.9	98.6
0°-90°	863.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	863.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1478	
5°	1438	133
15°	1086	298
25°	553	253
35°	185	121
45°	44	36
55°	10	9
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1268247

CATALOG NUMBER: P3AS20R459735D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1478.0
2.5°	1468.7
5°	1437.8
7.5°	1384.6
10°	1306.6
12.5°	1203.2
15°	1085.9
17.5°	955.5
20°	819.6
22.5°	681.5
25°	552.6
27.5°	435.3
30°	332.6
32.5°	250.1
35°	185.2
37.5°	136.6
40°	98.0
42.5°	67.9
45°	44.0
47.5°	24.7
50°	13.9
52.5°	10.8
55°	10.0
57.5°	9.3
60°	8.5
62.5°	7.7
65°	6.9
67.5°	6.2
70°	5.4
72.5°	4.6
75°	3.9
77.5°	3.1
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)