

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268263

Luminaire Tested: P3AS20R459735D010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459735D010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1760.0 lumens
Efficiency: N/A
Efficacy: 61.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268263
CATALOG NUMBER: P3AS20R459735D010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1268263

CATALOG NUMBER: P3AS20R459735D010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74			74
6	90	82	77	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70			70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62			62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59			59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	660934
5°	645453
10°	593331
15°	502750
20°	390051
25°	272677
30°	171773
35°	101134
40°	57221
45°	27817
50°	9654
55°	7837
60°	7587
65°	7368
70°	7052
75°	6693
80°	5935
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27817 cd/sqm



TEST NUMBER: P1268263
 CATALOG NUMBER: P3AS20R459735D010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.4	15.4
10°-20°	608.1	34.6
20°-30°	516.4	29.3
30°-40°	246.4	14.0
40°-50°	74.2	4.2
50°-60°	18.8	1.1
60°-70°	14.0	0.8
70°-80°	8.3	0.5
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1396.0	79.3
0°-40°	1642.3	93.3
0°-60°	1735.3	98.6
0°-90°	1760.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1760.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3014	
5°	2932	271
15°	2215	608
25°	1127	516
35°	378	246
45°	90	74
55°	20	19
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1268263
CATALOG NUMBER: P3AS20R459735D010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3014.1
2.5°	2995.2
5°	2932.3
7.5°	2823.7
10°	2664.7
12.5°	2453.8
15°	2214.6
17.5°	1948.6
20°	1671.5
22.5°	1389.8
25°	1127.0
27.5°	887.7
30°	678.4
32.5°	510.0
35°	377.8
37.5°	278.6
40°	199.9
42.5°	138.5
45°	89.7
47.5°	50.4
50°	28.3
52.5°	22.0
55°	20.5
57.5°	18.9
60°	17.3
62.5°	15.7
65°	14.2
67.5°	12.6
70°	11.0
72.5°	9.4
75°	7.9
77.5°	6.3
80°	4.7
82.5°	3.1
85°	1.6
87.5°	1.6
90°	0.0

(END OF REPORT)