

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267349

Luminaire Tested: P3AS13R159735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267349
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 461.0 lumens
Efficiency: N/A
Efficacy: 31.6 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267349

CATALOG NUMBER: P3AS13R159735DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1267349

CATALOG NUMBER: P3AS13R159735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	90	89
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	86	85
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	82	81
5	98	92	87	84	97	91	87	83	89	86	83	88	84	82	86	83	81	80	79	78
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	76	75
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	73	72
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	71	70
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	68	67
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	66	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	393806
5°	349570
10°	242770
15°	143565
20°	81767
25°	46745
30°	25852
35°	13786
40°	7614
45°	4124
50°	2559
55°	2026
60°	1754
65°	1608
70°	1410
75°	1525
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4124 cd/sqm

TEST NUMBER: P1267349

CATALOG NUMBER: P3AS13R159735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.0	29.3
10°-20°	178.2	38.7
20°-30°	91.8	19.9
30°-40°	34.5	7.5
40°-50°	11.3	2.4
50°-60°	4.8	1.0
60°-70°	3.1	0.7
70°-80°	1.8	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.0	87.9
0°-40°	439.5	95.3
0°-60°	455.6	98.8
0°-90°	461.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	461.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1796	
5°	1588	135
15°	632	178
25°	193	92
35°	52	34
45°	13	11
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1267349

CATALOG NUMBER: P3AS13R159735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1795.9
1°	1792.4
2°	1768.9
3°	1724.0
4°	1664.9
5°	1588.1
6°	1501.1
7°	1405.6
8°	1299.4
9°	1194.6
10°	1090.3
12.5°	838.9
15°	632.4
17.5°	473.4
20°	350.4
22.5°	261.6
25°	193.2
27.5°	140.8
30°	102.1
32.5°	72.4
35°	51.5
37.5°	36.9
40°	26.6
42.5°	19.1
45°	13.3
47.5°	9.8
50°	7.5
52.5°	6.2
55°	5.3
57.5°	4.4
60°	4.0
62.5°	3.6
65°	3.1
67.5°	2.7
70°	2.2
72.5°	2.2
75°	1.8
77.5°	1.3
80°	0.9
82.5°	0.9
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)