

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267413

Luminaire Tested: P3AS13R259735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 356.0 lumens
Efficiency: N/A
Efficacy: 24.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267413
CATALOG NUMBER: P3AS13R259735DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1267413
 CATALOG NUMBER: P3AS13R259735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84598
5°	82588
10°	76529
15°	68173
20°	58572
25°	49793
30°	40994
35°	31936
40°	22986
45°	14575
50°	8631
55°	5926
60°	5438
65°	5085
70°	4552
75°	4151
80°	3915
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14575 cd/sqm



TEST NUMBER: P1267413
 CATALOG NUMBER: P3AS13R259735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.8	9.8
10°-20°	83.4	23.4
20°-30°	94.2	26.5
30°-40°	74.5	20.9
40°-50°	37.6	10.6
50°-60°	15.1	4.2
60°-70°	9.7	2.7
70°-80°	5.3	1.5
80°-90°	1.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.3	59.6
0°-40°	286.8	80.6
0°-60°	339.5	95.4
0°-90°	356.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	356.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	386	
5°	375	35
15°	300	83
25°	206	94
35°	119	74
45°	47	38
55°	16	15
65°	10	10
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1267413
CATALOG NUMBER: P3AS13R259735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	385.8
1°	385.8
2°	384.5
3°	382.3
4°	379.2
5°	375.2
6°	370.3
7°	364.6
8°	358.3
9°	351.3
10°	343.7
11°	335.3
12°	327.3
13°	318.0
14°	309.1
15°	300.3
17.5°	275.4
20°	251.0
22.5°	228.0
25°	205.8
27.5°	184.1
30°	161.9
32.5°	141.0
35°	119.3
37.5°	99.3
40°	80.3
42.5°	62.5
45°	47.0
47.5°	35.0
50°	25.3
52.5°	19.1
55°	15.5
57.5°	14.2
60°	12.4
62.5°	11.1
65°	9.8
67.5°	8.4
70°	7.1
72.5°	6.2
75°	4.9
77.5°	4.0
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.4



TEST NUMBER: P1267413
CATALOG NUMBER: P3AS13R259735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)