

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267419

Luminaire Tested: P3AS13R259735DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267419
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259735DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 285.0 lumens
Efficiency: N/A
Efficacy: 19.5 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267419

CATALOG NUMBER: P3AS13R259735DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1267419

CATALOG NUMBER: P3AS13R259735DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103479
5°	99273
10°	86972
15°	69898
20°	53718
25°	40648
30°	29372
35°	19515
40°	11822
45°	6884
50°	4401
55°	3555
60°	3114
65°	2750
70°	2308
75°	2288
80°	1642
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6884 cd/sqm

TEST NUMBER: P1267419

CATALOG NUMBER: P3AS13R259735DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.1	14.4
10°-20°	85.1	29.9
20°-30°	77.0	27.0
30°-40°	46.3	16.2
40°-50°	18.4	6.4
50°-60°	8.5	3.0
60°-70°	5.2	1.8
70°-80°	2.8	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.2	71.3
0°-40°	249.4	87.5
0°-60°	276.3	97.0
0°-90°	285.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	285.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	472	
5°	451	41
15°	308	85
25°	168	77
35°	73	46
45°	22	18
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1267419

CATALOG NUMBER: P3AS13R259735DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	471.9
1°	471.9
2°	469.6
3°	464.8
4°	458.5
5°	451.0
6°	441.2
7°	430.1
8°	417.2
9°	404.3
10°	390.6
11°	374.6
12°	358.1
13°	341.7
14°	325.2
15°	307.9
17.5°	267.0
20°	230.2
22.5°	196.8
25°	168.0
27.5°	140.8
30°	116.0
32.5°	93.3
35°	72.9
37.5°	55.5
40°	41.3
42.5°	30.2
45°	22.2
47.5°	16.9
50°	12.9
52.5°	10.7
55°	9.3
57.5°	8.0
60°	7.1
62.5°	5.8
65°	5.3
67.5°	4.4
70°	3.6
72.5°	3.1
75°	2.7
77.5°	2.2
80°	1.3
82.5°	0.9
85°	0.9
87.5°	0.4



TEST NUMBER: P1267419

CATALOG NUMBER: P3AS13R259735DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)