

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267445

Luminaire Tested: P3AS13R309735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267445
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 362.0 lumens
Efficiency: N/A
Efficacy: 24.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267445

CATALOG NUMBER: P3AS13R309735DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1267445

CATALOG NUMBER: P3AS13R309735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85519
5°	83601
10°	77732
15°	69172
20°	59505
25°	50398
30°	41829
35°	32819
40°	23530
45°	15443
50°	8801
55°	5773
60°	5438
65°	5085
70°	4552
75°	4151
80°	3915
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15443 cd/sqm

TEST NUMBER: P1267445

CATALOG NUMBER: P3AS13R309735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.3	9.7
10°-20°	84.7	23.4
20°-30°	95.5	26.4
30°-40°	76.2	21.1
40°-50°	39.2	10.8
50°-60°	14.7	4.1
60°-70°	9.7	2.7
70°-80°	5.2	1.4
80°-90°	1.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	215.4	59.5
0°-40°	291.7	80.6
0°-60°	345.6	95.5
0°-90°	362.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	362.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	390	
5°	380	35
15°	305	85
25°	208	95
35°	123	76
45°	50	39
55°	15	15
65°	10	10
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1267445

CATALOG NUMBER: P3AS13R309735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	390.0
1°	390.0
2°	388.7
3°	386.5
4°	383.4
5°	379.8
6°	375.4
7°	369.6
8°	363.4
9°	356.3
10°	349.1
11°	341.2
12°	332.7
13°	323.8
14°	314.5
15°	304.7
17.5°	279.9
20°	255.0
22.5°	231.0
25°	208.3
27.5°	186.1
30°	165.2
32.5°	143.9
35°	122.6
37.5°	101.7
40°	82.2
42.5°	64.9
45°	49.8
47.5°	36.9
50°	25.8
52.5°	18.2
55°	15.1
57.5°	13.8
60°	12.4
62.5°	11.1
65°	9.8
67.5°	8.4
70°	7.1
72.5°	5.8
75°	4.9
77.5°	4.0
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.4



TEST NUMBER: P1267445

CATALOG NUMBER: P3AS13R309735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)