

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267458

Luminaire Tested: P3AS13R309735DE010 E3PHLD1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1267458  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R309735DE010 E3PHLD1MW  
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 704.0 lumens  
Efficiency: N/A  
Efficacy: 48.2 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267458  
CATALOG NUMBER: P3AS13R309735DE010 E3PHLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1267458

CATALOG NUMBER: P3AS13R309735DE010 E3PHLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	94	93	91	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	80	76	73	71
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	74	70	66	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	69	64	61	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	48	56	51	48	46
9	68	57	50	45	66	56	49	45	55	49	45	54	49	45	53	48	44	53	48	44	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	173473
5°	165815
10°	143017
15°	118548
20°	97168
25°	78343
30°	63124
35°	51718
40°	42966
45°	36438
50°	31180
55°	26952
60°	24033
65°	21014
70°	18401
75°	15504
80°	11491
85°	6542

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 36438 cd/sqm



TEST NUMBER: P1267458  
 CATALOG NUMBER: P3AS13R309735DE010 E3PHLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.3	9.7
10°-20°	145.6	20.7
20°-30°	149.2	21.2
30°-40°	122.0	17.3
40°-50°	91.3	13.0
50°-60°	64.1	9.1
60°-70°	40.3	5.7
70°-80°	19.4	2.8
80°-90°	3.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.2	51.6
0°-40°	485.1	68.9
0°-60°	640.5	91.0
0°-90°	704.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	704.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	791	
5°	753	68
15°	522	146
25°	324	149
35°	193	122
45°	118	91
55°	70	64
65°	40	40
75°	18	19
85°	3	4
90°	0	



TEST NUMBER: P1267458  
CATALOG NUMBER: P3AS13R309735DE010 E3PHLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	791.1
2.5°	783.3
5°	753.3
7.5°	703.6
10°	642.3
12.5°	582.2
15°	522.2
17.5°	467.4
20°	416.4
22.5°	368.1
25°	323.8
27.5°	284.6
30°	249.3
32.5°	220.6
35°	193.2
37.5°	171.0
40°	150.1
42.5°	133.2
45°	117.5
47.5°	103.1
50°	91.4
52.5°	80.9
55°	70.5
57.5°	62.7
60°	54.8
62.5°	47.0
65°	40.5
67.5°	33.9
70°	28.7
72.5°	23.5
75°	18.3
77.5°	13.1
80°	9.1
82.5°	5.2
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)