

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268345

Luminaire Tested: P3AS20R609735D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268345
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609735D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1298.0 lumens
Efficiency: N/A
Efficacy: 45.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268345

CATALOG NUMBER: P3AS20R609735D010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1268345

CATALOG NUMBER: P3AS20R609735D010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230420
5°	227822
10°	219947
15°	207788
20°	191537
25°	173429
30°	153973
35°	131571
40°	104625
45°	73775
50°	44075
55°	22288
60°	21402
65°	19613
70°	18208
75°	17368
80°	15911
85°	11825

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 73775 cd/sqm

TEST NUMBER: P1268345

CATALOG NUMBER: P3AS20R609735D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.3	7.5
10°-20°	255.8	19.7
20°-30°	328.5	25.3
30°-40°	304.5	23.5
40°-50°	185.4	14.3
50°-60°	61.8	4.8
60°-70°	37.6	2.9
70°-80°	21.2	1.6
80°-90°	6.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	681.5	52.5
0°-40°	986.0	76.0
0°-60°	1233.2	95.0
0°-90°	1298.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1298.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1051	
5°	1035	97
15°	915	256
25°	717	328
35°	492	305
45°	238	185
55°	58	62
65°	38	38
75°	20	21
85°	5	6
90°	0	

TEST NUMBER: P1268345

CATALOG NUMBER: P3AS20R609735D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1050.8
2.5°	1046.0
5°	1035.0
7.5°	1014.5
10°	987.8
12.5°	954.7
15°	915.3
17.5°	869.6
20°	820.8
22.5°	768.8
25°	716.8
27.5°	663.2
30°	608.1
32.5°	553.0
35°	491.5
37.5°	426.9
40°	365.5
42.5°	300.9
45°	237.9
47.5°	184.3
50°	129.2
52.5°	77.2
55°	58.3
57.5°	53.6
60°	48.8
62.5°	42.5
65°	37.8
67.5°	33.1
70°	28.4
72.5°	23.6
75°	20.5
77.5°	15.8
80°	12.6
82.5°	7.9
85°	4.7
87.5°	3.2
90°	0.0

(END OF REPORT)