

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267492

Luminaire Tested: P3AS13R409735DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267492
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409735DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1271.9 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267492
CATALOG NUMBER: P3AS13R409735DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1267492
 CATALOG NUMBER: P3AS13R409735DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92			
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89			
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85			
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82			
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79			
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76			
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	73			
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71			
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	669749
5°	666518
10°	644789
15°	570469
20°	372199
25°	131862
30°	27954
35°	9209
40°	3378
45°	1116
50°	921
55°	1032
60°	789
65°	934
70°	577
75°	763
80°	1137
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 1512 cd/sqm



TEST NUMBER: P1267492
 CATALOG NUMBER: P3AS13R409735DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.9	22.4
10°-20°	663.5	52.2
20°-30°	287.9	22.6
30°-40°	26.5	2.1
40°-50°	3.8	0.3
50°-60°	2.3	0.2
60°-70°	1.7	0.1
70°-80°	1.0	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1236.4	97.2
0°-40°	1262.9	99.3
0°-60°	1269.0	99.8
0°-90°	1271.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1271.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3054	
5°	3028	285
15°	2513	664
25°	545	288
35°	34	27
45°	4	4
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1267492
CATALOG NUMBER: P3AS13R409735DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3054.3
2.5°	3050.6
5°	3028.0
7.5°	2980.0
10°	2895.8
12.5°	2753.7
15°	2512.9
17.5°	2113.7
20°	1595.0
22.5°	1035.6
25°	545.0
27.5°	234.5
30°	110.4
32.5°	59.7
35°	34.4
37.5°	20.8
40°	11.8
42.5°	6.3
45°	3.6
47.5°	2.7
50°	2.7
52.5°	2.7
55°	2.7
57.5°	2.7
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.8
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)