

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267497

Luminaire Tested: P3AS13R409735DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267497
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409735DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1268.0 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267497

CATALOG NUMBER: P3AS13R409735DE010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1267497

CATALOG NUMBER: P3AS13R409735DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	646330
5°	641667
10°	624860
15°	558187
20°	370122
25°	138661
30°	37094
35°	14509
40°	5210
45°	2481
50°	751
55°	344
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2481 cd/sqm

TEST NUMBER: P1267497

CATALOG NUMBER: P3AS13R409735DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.1	21.7
10°-20°	651.5	51.4
20°-30°	295.5	23.3
30°-40°	38.3	3.0
40°-50°	6.6	0.5
50°-60°	0.8	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1222.0	96.4
0°-40°	1260.3	99.4
0°-60°	1267.7	100.0
0°-90°	1268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1268.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2948	
5°	2915	275
15°	2459	651
25°	573	295
35°	54	38
45°	8	7
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1267497

CATALOG NUMBER: P3AS13R409735DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2947.5
1°	2945.7
2°	2941.3
3°	2934.6
4°	2926.2
5°	2915.1
6°	2902.2
7°	2886.2
8°	2866.7
9°	2840.1
10°	2806.3
11°	2766.8
12°	2714.0
13°	2648.8
14°	2563.5
15°	2458.8
16°	2325.1
17°	2172.9
18°	1990.0
19°	1796.9
20°	1586.1
21°	1375.2
22°	1167.5
23°	960.6
24°	757.3
25°	573.1
26°	424.4
27°	310.7
28°	233.5
29°	181.6
30°	146.5
31°	121.2
32°	101.2
32.5°	92.3
33°	83.5
34°	67.9
35°	54.2
36°	42.6
37°	33.7
37.5°	30.2
38°	26.6
39°	22.2
40°	18.2
42.5°	12.0
45°	8.0



TEST NUMBER: P1267497

CATALOG NUMBER: P3AS13R409735DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	4.9
50°	2.2
52.5°	0.9
55°	0.9
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)